

# ProPEX® Brass Sweat Adapter

Submittal Information  
Revision B: Feb. 4, 2010

## Project Information

Job Name:

Location:

Part No. Ordered:

Engineer:

Date Submitted:

Contractor:

Submitted By:


Manufacturer's Representative:

Approved By:

## Technical Data

Material:

CA 360 Brass



## Product Information and Application Use

ProPEX® Brass Sweat Adapters transition Uponor PEX tubing to copper pipe.<sup>1</sup> These adapters are approved for use in hot and cold potable water systems, hydronic radiant heating systems and the AquaSAFE™ Residential Fire Safety System. These adapters are safe for direct burial in soil.

✓ Description	Part Number	A	B	C	Weight
ProPEX Brass Sweat Adapter, 3/8" PEX x 1/2" Copper	Q4513850	1.32"	0.721"	0.50" CU	0.07 lbs.
ProPEX Brass Sweat Adapter, 1/2" PEX x 1/2" Copper	Q4515050	1.44"	0.750"	0.50" CU	0.08 lbs.
ProPEX Brass Sweat Adapter, 1/2" PEX x 3/4" Copper	Q4515075	1.63"	0.989"	0.75" CU	0.16 lbs.
ProPEX Brass Sweat Adapter, 5/8" PEX x 1/2" Copper	Q4516350	1.60"	0.910"	0.50" CU	0.11 lbs.
ProPEX Brass Sweat Adapter, 5/8" PEX x 3/4" Copper	Q4516375	2.00"	0.989"	0.75" CU	0.16 lbs.
ProPEX Brass Sweat Adapter, 3/4" PEX x 1/2" Copper	Q4517550	1.67"	1.070"	0.50" CU	0.30 lbs.
ProPEX Brass Sweat Adapter, 3/4" PEX x 3/4" Copper*	Q4517575	2.04"	1.070"	0.75" CU	0.20 lbs.
ProPEX Brass Sweat Adapter, 3/4" PEX x 1" Copper	Q4517510	2.17"	1.258"	1.00" CU	0.31 lbs.
ProPEX Brass Sweat Adapter, 1" PEX x 1" Copper*	Q4511010	2.40"	1.345"	1.00" CU	0.30 lbs.
ProPEX Brass Sweat Adapter, 1 1/4" PEX x 1 1/4" Copper	Q4511313	2.63"	1.640"	1.25" CU	0.40 lbs.
ProPEX Brass Sweat Adapter, 1 1/2" PEX x 1 1/2" Copper	Q4511515	2.75"	1.875"	1.50" CU	0.50 lbs.
ProPEX Brass Sweat Adapter, 2" PEX x 2" Copper	Q4512020	3.53"	3.00"	2.00" CU	0.80 lbs.

## Installation

Use the appropriate Uponor ProPEX Ring for the tubing (sold separately). Do not solder within 18 inches of the ProPEX Fitting. Refer to the AquaPEX® Professional Plumbing Installation Guide, Radiant Floor Heating Installation Handbook or AquaSAFE Residential Fire Sprinkler Installation Guide for additional information.

## Standards

CAN/CSA B137.5; ASTM F877; ASTM F1960

## Codes

IPC; UPC; NSPC; NPC of Canada

## Listings

HUD MR 1269; ICC ESR 1099; ANSI/NSF 14- and 61-certified; \*UL 1821; \*ULC/ORD C199P

## Related Applications

PEX-a Plumbing Systems  
Uponor Residential Fire Safety Systems  
Radiant Heating and Cooling Systems

## Contact Information

Uponor, Inc.  
5925 148<sup>th</sup> Street West  
Apple Valley, MN 55124 USA  
Phone: (800) 321-4739  
Fax: (952) 891-1409  
www.uponor-usa.com

Uponor Ltd.  
2000 Argenta Rd., Plaza 1, Ste. 200  
Mississauga, ON L5N 1W1 CANADA  
Phone: (888) 994-7726  
Fax: (800) 638-9517  
www.uponor.ca

<sup>1</sup>ProPEX® is a registered trademark of Uponor, Inc. ProPEX™ is a trademark of Uponor Ltd.