

ProPEX® Brass Female Threaded Adapter

Submittal Information

Revision B: Feb. 4, 2010

Project Information

Job Name:

Location:

Part No. Ordered:

Engineer:

Date Submitted:

Contractor:

Submitted By:

Manufacturer's Representative:

Approved By:


Technical Data

Material:

CA 360 Brass

Product Information and Application Use

The ProPEX® Brass Female Threaded Adapter connects Uponor PEX tubing to female NPT threads.¹ These fittings are used in hot and cold domestic potable water systems or in any radiant heating system. One end of the adapter is manufactured with the Uponor ProPEX Fitting for connections to Wirsbo hePEX™ tubing or Uponor AquaPEX® tubing. The other end of the adapter connects to female threaded connections. These adapters are safe for direct burial in soil.



✓ Description	Part Number	A	B	C	Weight
ProPEX Brass Female Threaded Adapter, 1/2" PEX x 1/2" NPT	Q4575050	1.57"	1.000" HEX	0.50" NPT	0.20 lbs.
ProPEX Brass Female Threaded Adapter, 1/2" PEX x 3/4" NPT	Q4575075	1.75"	1.187" HEX	0.75" NPT	0.40 lbs.
ProPEX Brass Female Threaded Adapter, 5/8" PEX x 3/4" NPT	Q4576375	1.91"	1.187" HEX	0.75" NPT	0.20 lbs.
ProPEX Brass Female Threaded Adapter, 3/4" PEX x 3/4" NPT*	Q4577575	1.87"	1.375" HEX	0.75" NPT	0.20 lbs.
ProPEX Brass Female Threaded Adapter, 3/4" PEX x 1" NPT	Q4577510	2.21"	1.500" HEX	1.00" NPT	0.40 lbs.
ProPEX Brass Female Threaded Adapter, 1" PEX x 3/4" NPT	Q4571075	2.17"	1.187" HEX	0.75" NPT	0.25 lbs.
ProPEX Brass Female Threaded Adapter, 1" PEX x 1" NPT	Q4571010	2.44"	1.500" HEX	1.00" NPT	0.45 lbs.
ProPEX Brass Female Threaded Adapter, 1 1/4" PEX x 1 1/4" NPT	Q4571313	2.57"	2.000" HEX	1.25" NPT	1.00 lbs.
ProPEX Brass Female Threaded Adapter, 1 1/2" PEX x 1 1/2" NPT	Q4571515	2.75"	2.500" HEX	1.50" NPT	2.20 lbs.
ProPEX Brass Female Threaded Adapter, 2" PEX x 2" NPT	Q4572020	3.53"	3.000" HEX	2.00" NPT	2.20 lbs.

Installation

ProPEX Tool and ProPEX Rings (sold separately) are required for connecting the PEX tubing. For more information, refer to the AquaPEX Professional Plumbing Installation Guide or the Radiant Floor Heating Installation Handbook.

Standards

CAN/CSA B137.5; ASTM F877; ASTM F1960

Codes

IPC; UPC; NSPC; NPC of Canada

Listings

ANSI/NSF 14- and 61-certified; ICC ESR 1099; HUD MR 1269; *UL 1821; *ULC/ORD C199P

Related Applications

PEX-a Plumbing Systems
Radiant Heating and Cooling Systems
Uponor Residential Fire Safety Systems

Contact Information

Uponor, Inc.
5925 148th Street West
Apple Valley, MN 55124 USA
Phone: (800) 321-4739
Fax: (952) 891-1409
www.uponor-usa.com

Uponor Ltd.
2000 Argentia Rd., Plaza 1, Ste. 200
Mississauga, ON L5N 1W1 CANADA
Phone: (888) 994-7726
Fax: (800) 638-9517
www.uponor.ca

¹ProPEX® is a registered trademark of Uponor, Inc. ProPEX™ is a trademark of Uponor Ltd.