

Tankless Water Heaters Kit • Spec Sheet



Tankless Water Heater Kit Includes

- 1 Hot Valve
- 1 Cold Valve
- 1 Pressure Relief Valve

See Following Pages for Detailed Information

 **MATCO-NORCA**
Global sourcing. National compliance. Local service.

NEW YORK PO Box 27, Rt. 22, Brewster NY 10509 • Toll Free: 800-431-2082 • Fax: 845-278-9056
TEXAS 1150 Silber Rd., Houston TX 77055 • Toll Free: 800-935-5456 • Fax: 713-680-2999
CALIFORNIA 5593 Fresca Dr., La Palma CA 90623 • Toll Free: 866-532-8306 • Fax: 866-532-8307
WEB: www.matco-norca.com EMAIL: mail@matco-norca.com

Tankless Water Heaters - Hot • Spec Sheet



FEATURES & BENEFITS


- 600# Rating (Non-Shock)
- Full Port, 1/4 Turn Design
- Blow-Out Proof Stem
- Adjustable Packing
- Integral Hose End Drain / Purge Port with Cap
- Integral 3/4" FNPT Relief Valve Port (9601, 9621 Hot Valve)
- Available in: Union X Threaded & Union X Solder Ends
- Size 3/4"

DIMENSIONS

Part #	Size	Description
TV04TH	3/4"	IPS
TV04CH	3/4"	C X C

MATERIAL SPECIFICATIONS

No.	Part	Material
1	Plugs	Brass
2	Rubber Washer	EPDM
3	Male Bonnet	Brass
4	Seats	PTFE
5	Ball	Brass
6	Packing Gland	PTFE
7	Brass Disk	Brass
8	Stem	Brass
9	Packing Nut	Brass
10	Chain	PVC
11	Handle	Aluminum Alloy
12	Metal Disk	Steel
13	Screw	Steel
14	Hex Nut	Steel
15	Handle T	Aluminum Alloy
16	O - Ring	EPDM
17	Body	Brass
18	Seats	PTFE
19	Ball	Brass
20	Bonnet	Brass
21	O - Ring	EPDM
22	Tail Piece	Brass
23	Gasket	POM
24	Union Nut	Brass



MATCO-NORCA
Global sourcing. National compliance. Local service.

NEW YORK PO Box 27, Rt. 22, Brewster NY 10509 • Toll Free: 800-431-2082 • Fax: 845-278-9056
TEXAS 1150 Silber Rd., Houston TX 77055 • Toll Free: 800-935-5456 • Fax: 713-680-2999
CALIFORNIA 5593 Fresca Dr., La Palma CA 90623 • Toll Free: 866-532-8306 • Fax: 866-532-8307
 WEB: www.matco-norca.com EMAIL: mail@matco-norca.com

Tankless Water Heaters - Cold • Spec Sheet



FEATURES & BENEFITS


- 600# Rating (Non-Shock)
- Full Port, 1/4 Turn Design
- Blow-Out Proof Stem
- Adjustable Packing
- Integral Hose End Drain / Purge Port with Cap
- Integral 3/4" FNPT Relief Valve Port (9601, 9622 Cold Valve)
- Available in: Union X Threaded & Union X Solder Ends
- Size 3/4"

DIMENSIONS

Part #	Size	Description
TV04TC	3/4"	IPS
TV04CC	3/4"	C X C

MATERIAL SPECIFICATIONS

No.	Part	Material
1	Plugs	Brass
2	Rubber Washer	EPDM
3	Male Bonnet	Brass
4	Seats	PTFE
5	Ball	Brass
6	Packing Gland	PTFE
7	Brass Disk	Brass
8	Stem	Brass
9	Packing Nut	Brass
10	Chain	PVC
11	Handle	Aluminum Alloy
12	Metal Disk	Steel
13	Screw	Steel
14	Hex Nut	Steel
15	Handle T	Aluminum Alloy
16	O - Ring	EPDM
17	Body	Brass
18	Seats	PTFE
19	Ball	Brass
20	Bonnet	Brass
21	O - Ring	EPDM
22	Tail Piece	Brass
23	Gasket	POM
24	Union Nut	Brass



MATCO-NORCA
Global sourcing. National compliance. Local service.

PRV04CA Pressure Relief Valve • Spec Sheet



FEATURES & BENEFITS


- 150# IPS Valve For Tankless Water Heater Kits
- Designed for the Protection of Hot Water Supply Systems
- Valve Automatically Reseats After Pressure Relief
- Compact and Economical
- Installed Directly on the Tank or in a Tee
- Can go on Either Side of the Water Heater.
- 125 PSI and 150 PSI Rated @ 500,000 btu/hr
- ASME Section IV Certified
- ANSI Z21.22 and CSA 4.4 Certified
- Size 3/4"

MATERIAL SPECIFICATIONS

Part	Material
Body	Bronze
Seat Disc	Silicone
Pressure Spring	Stainless Steel
Internal Part	Brass & Stainless Steel

DIMENSIONS

Part #	Size	A	B	C
PRV04CA	3/4"	1-1/4"	1-9/16"	1-13/16"



 **MATCO-NORCA**
Global sourcing. National compliance. Local service.