

For Commercial & Residential Applications

Job Name _____

Contractor _____

Job Location _____

Approval _____

Engineer _____

Contractor's P.O. No. _____


Approval _____

Representative _____


Metal Dishwasher Tailpieces



For Copper Tubing



For Hose and Copper Tubing



MODEL	✓TO SUBMIT	DESCRIPTION	DIMENSIONS						FINISH
			A		B		C		
			in.	mm.	in.	mm.			
For 1/2" copper tubing									
760 151		1 1/2" x 6"	6	152	4 1/4	108	22 GA.	Rough Brass	
760 152		1 1/2" x 6"	6	152	4 1/4	108	22 GA.	Chrome	
761 151		1 1/2" x 8"	8	203	6 1/2	165	22 GA.	Rough Brass	
761 151B		1 1/2" x 8", w/brass nut	8	203	6 1/2	165	20 GA.	Rough Brass	
761 152		1 1/2" x 8"	8	203	6 1/2	165	22 GA.	Chrome	
763 151		1 1/2" x 12"	12	305	10	254	22 GA.	Rough Brass	
763 251		1 1/2" x 12", long branch	12	305	11 1/2	292	22 GA.	Rough Brass	
763 171B		1 1/2" x 12", w/brass nut	12	305	10	254	17 GA.	Rough Brass	
For 3/4" copper tubing									
760 002		1 1/2" x 6"	6	152	4 1/2	114	22 GA.	Chrome	
761 001		1 1/2" x 8"	8	203	6 1/2	165	22 GA.	Rough Brass	
761 002		1 1/2" x 8"	8	203	6 1/2	165	22 GA.	Chrome	
763 001		1 1/2" x 12"	12	305	10	254	22 GA.	Rough Brass	
762 003S		1 1/4" x 8", solder joint top	8	203	6 1/2	165	20 GA.	Chrome	
762 003T		1 1/4" x 8", threaded top	8	203	6 1/2	165	20 GA.	Chrome	
For 3/4" hose and 1/2" copper tubing									
761 101		1 1/2" x 8"	8	203	6	152	22 GA.	Rough Brass	
761 102		1 1/2" x 8"	8	203	6	152	22 GA.	Chrome	
763 101		1 1/2" x 12"	12	305	10 1/4	260	22 GA.	Rough Brass	



815 Chestnut Street • N. Andover, MA 01845
 Tell: 978.688.1811 Fax: 978.794.1848
www.wattsbrass-tubular.com

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.