




Dimensional Documentation



Cap C				
Stock Code	Size	Material	L (in)	D (in)
	d			
77712	1/2"	Copper	0.917	0.799
77717	3/4"	Copper	1.067	0.945
77722	1"	Copper	1.110	0.992
77727	1-1/4"	Copper	1.181	1.024
77732	1-1/2"	Copper	1.622	1.465
77737	2"	Copper	1.811	1.575




Adapter Flange C x Flange (Old Version)									
Stock Code	Size	Material	L (in)	Z (in)	b1 (in)	b2 (in)	D (in)	K (in)	d2 (in)
	d1								
19708	1"	Bronze	2.756	1.850	0.630	0.827	4.331	3.110	0.630
19713	1-1/4"	Bronze	2.756	1.850	0.630	0.827	4.528	3.504	0.630
19718	1-1/2"	Bronze	3.071	1.654	0.630	0.827	4.921	3.858	0.630
19723	2"	Bronze	3.661	2.087	0.630	0.827	5.906	4.764	0.748




PureFlow/ProPress Adapter PEX x C				
Stock Code	Size	Material	L (in)	Z (in)
	d x d1			
67620	1/2"-1/2"	Copper	1.575	0.236
67626	1/2"-3/4"	Copper	1.831	0.335
67627	5/8"-1/2"	Copper	1.496	0.157
67628	5/8"-3/4"	Copper	1.831	0.335
67630	3/4"-1/2"	Copper	1.417	0.079
67640	3/4"-3/4"	Copper	1.732	0.236
67660	1"-1"	Copper	1.969	0.315


Dimensional Documentation




Elbow 45° C x C				
Stock Code	Material	Size	Z (in)	L (in)
		d		
91417	Bronze	2-1/2"	1.083	3.248
91422	Bronze	3"	1.181	3.346
91427	Bronze	4"	1.358	3.917



Cap C				
Stock Code	Material	Size	Z (in)	L (in)
		d R _p		
91432	Bronze	2-1/2"x 3/4" NPT	0.827	2.992
91437	Bronze	3"x 3/4" NPT	0.846	3.012
91442	Bronze	4"x 3/4" NPT	0.945	3.504




Adapter Flange C x Flange (old version)								
Stock Code	Material	Size	Z (in)	L (in)	b (in)	d ₂ (in)	D (in)	k (in)
		d ₁						
91567		2-1/2"	0.827	21	2.933	0.571	0.748	7.008
91572		3"	0.866	22	2.953	0.630	0.748	7.500
91577		4"	0.551	14	3.051	0.689	0.748	9.016



Adapter Flange C x Flange (new version)									
Stock Code	Material	Size	Z (in)	L (in)	b ₁ (in)	b ₂ (in)	k (in)	D (in)	d ₂ (in)
		d ₁							
19728	Bronze	2-1/2"	0.984	3.091	0.787	0.827	5.512	7.087	0.748
19733	Bronze	3"	1.024	3.150	0.787	0.906	5.984	7.480	0.748
19738	Bronze	4"	0.630	3.150	0.807	0.906	7.520	9.055	0.748


Dimensional Documentation

viega




Adapter Flange P x Flange (Copper/Steel)

Stock Code	Size	Z (in)	L (in)	b (in)	k (in)	D (in)	d2 (in)
	d1						
20853	2-1/2"	1.102	2.795	0.787	5.512	7.087	0.748
20858	3"	1.201	3.169	0.787	5.984	7.480	0.748
20863	4"	1.204	3.602	0.807	7.520	9.055	0.748




Cap P (Copper)

Stock Code	Size	Z (in)	L (in)
	d		
20833	2-1/2"	1.339	3.031
20643	3"	1.358	3.327
20848	4"	1.398	3.760



XL-C Reducer P x P (Copper)

Stock Code	Size	Z (in)	L (in)
	D R		
20685	2-1/2" x 1"	1.759	4.358
20690	2-1/2" x 1-1/4"	1.610	4.338
20695	2-1/2" x 1-1/2"	1.519	4.637
20700	2-1/2" x 2"	1.413	4.688
20705	3" x 1-1/2"	1.775	5.173
20710	3" x 2"	1.527	5.078
20715	3" x 2-1/2"	1.405	5.066
20720	4" x 2"	2.055	5.999
20725	4" x 2-1/2"	1.933	5.938
20730	4" x 3"	1.700	6.031



XL-C Reducer P x P (Copper)

Stock Code	Size	Z1 (in)	Z2 (in)	L1 (in)	L2 (in)
	d d Rp				
20868	4" x 4" x 2"	1.594	2.598	3.957	3.287
20873	4" x 4" x 3/4"	0.965	2.461	3.327	3.071
20878	2-1/2" x 2-1/2" x 2"	1.535	1.831	3.228	2.520
20883	2-1/2" x 2-1/2" x 3/4"	0.906	1.693	2.598	2.303
20893	3" x 3" x 3/4"	0.925	1.949	2.894	2.559
20888	3" x 3" x 3"	1.555	1.984	3.523	2.854

Viega... The global leader in plumbing, heating and pipe joining systems.

301 N. Main, 9th Floor • Wichita, KS 67202 • Ph: 800-976-9819 • Fax: 316-425-7618 • E-Mail: insidesales@viega.com • www.viega.com