

# Ox Box™

NEW

## Gas Outlet Box



- **ACCESSIBLE**

1/4-turn ball valve for easy, secure, accessible operation

- **VERSATILE**

Box is available for 1/2" or 3/4" iron-pipe applications or 1/2" CSST applications in both standard and fire-rated products

- **STRENGTH**

Recessed box is made of high-impact ABS providing the strongest finished installation for all gas appliance needs

- **CERTIFIED**

Valve has CSA certification to ANSI Z21.15-1997 / CGA 9.1-M97



Supply • Drainage • Support • Testing • Specialties • Tools • Access

**Sioux Chief**   
MANUFACTURING SINCE 1957

## Gas Ox Box Benefits

- Frame Extension (696-EX): extends box face for installations thicker than ½" drywall
- Solid Frame Insert (696-SC): can be cut as desired to fit around gas lines for flush cover
- Box/frame can be painted or wallpapered and has a modern beveled frame
- Iron Pipe test plug included in each gas box installation kit.
- Residential, commercial, and industrial direct connect application include: gas range, wall heater, water heater, garage heater supply, furnaces, laundry washers and dryers.

## Additional Ox Box Outlet Boxes for Washing Machine and Ice Maker



## Additional Sioux Chief Products

### Tools and Gas Products



#### Tools

Heavy duty pipe wrench and adjustable pliers



#### Gas Products

Gas ball valves, angled and straight log lighter valves, log lighter bars

## Installations

Before installing: Make sure valve and gas source are turned off and line is purged before installation.

- 1 Set Ox Box supply box directly to stud and/or on support bracket.
- 2 Insert supplied valve adapter through hole in the box and hand tighten locknut.
- 3 Apply pipe thread sealant to male threads and tighten supply piping. Tighten locknut with a wrench. For CSST, follow applicable manufacturer's installation instructions for adapter.
- 4 Apply pipe thread sealant to bottom of valve and tighten. Do not overtighten.
- 5 Check all connections for leaks using leak detector.
- 6 Turn off gas supply and connect appliance according to manufacturers instructions.

Note: Use appropriate and code mandated pipe protection and insulation. Consult all local and applicable building/gas codes prior to and during installation and testing. Use box for indoor applications only. Keep flame or other combustion sources away during installation.



Item No.	Connection	Pkg	Min. Qty	Case Qty	List Price
<b>GAS OX BOX</b>					
696-1021GF	½" NPT valve and adapter for iron pipe, bagged	B	6	6	28.99 EA
696-1031GF	¾" NPT valve and adapter for iron pipe, bagged	B	6	6	32.40 EA
696-1020GF	½" FIP valve for CSST connection, bagged	B	6	6	26.00 EA
<b>FIRE-RATED GAS OX BOX</b>					
696R1021GF	½" NPT valve and adapter for iron pipe, bagged	B	6	6	73.21 EA
696R1031GF	¾" NPT valve and adapter for iron pipe, bagged	B	6	6	76.62 EA
696R1020GF	½" FIP valve for CSST connection, bagged	B	6	6	70.22 EA
<b>OX BOX ACCESSORIES</b>					
696-EX	Frame extension	B	10	10	3.25 EA
696-SC	Solid frame insert	B	10	10	4.00 EA

Packaging Codes || B: bulk

## DISTRIBUTED BY

24110 South Peculiar Drive  
Peculiar, Missouri 64078  
tel: 1-800-821-3944  
fax: 1-800-758-5950  
www.siuoxchief.com

