

Aprilaire Wi-Fi Thermostats with SmartIAQ

Aprilaire[®]
Your Partners in Comfort[®]



Aprilaire Wi-Fi Thermostats



For 75 years, Aprilaire has been committed to the success of HVAC contractors by providing solutions designed for consumer health, comfort, protection and energy savings. Our new line of Wi-Fi thermostats continues that tradition.

Clean and simple, the Aprilaire Wi-Fi Thermostat app has intuitive temperature control features designed so anyone can understand and use them to effectively deliver comfort and energy savings.

But that's not all. Aprilaire, the #1 provider of indoor air quality solutions, also offers SmartIAQ: the ability to balance all aspects of indoor air quality, including Temperature, Humidity, Air Purity and Fresh Air.

Energy Savings—without Sacrificing Comfort

ENERGY STAR® stopped certifying programmable thermostats because consumers found them difficult to use. Aprilaire Wi-Fi Thermostats offer an accessible, simple user interface for control features anyone can use. These include:

Schedule Programming


Intuitive program setup and adjustment with a graphical, friendly design.

Away and Heat Blast

When activated, the system automatically adjusts the temperature when leaving or arriving and can temporarily override an established program.

Peace of Mind and Protection

Email alerts that immediately and proactively notify the homeowner when failures occur, temperature and RH levels are exceeded, or when service or maintenance is needed.



* Source data: Energy Star®

SmartIAQ

Offer your customers the ability to control all configurations of heating/cooling and IAQ accessories including Humidifier, Dehumidifier, Air Cleaner and Ventilator. All installed products are conveniently controlled from one app.

Product Portfolio

The Aprilaire Wi-Fi product portfolio is designed to offer consumers a variety of key features and price points. From customers who require only temperature control at an attractive price point to those who want to control all aspects of IAQ in one simple interface, Aprilaire makes it easy to select the right product.

	8810	8820 ²	8830 ²	8840 ²
Temperature	☑	☑	☑	☑
Air Cleaning	☑	☑	☑	☑
Humidity		☑ ¹	☑	☑
Fresh Air		☑ ¹	☑	☑

¹ Controls either humidity or fresh air ventilation with only one relay.

² App automatically configures; removing functionality if removed from the thermostat.



Model 8840 IAQ Control

Industry's first color touch screen with all control options on the home screen.

- + Universal 3H/3C or 4H/2C HP
- + Event-Based™ Air Cleaning
- + Humidity and Ventilation
- + 2 Part - 3-Wire design
- + Wi-Fi with full color touch screen



Model 8830 IAQ Control

Easy-to-use touch screen with all control options on the home screen.

- + Universal 3H/3C or 4H/2C HP
- + Event-Based™ Air Cleaning
- + Humidity and Ventilation
- + 2 Part - 3-Wire design
- + Wi-Fi touch screen



Model 8820

Easy to use touch screen designed for temperature and humidity control.

- + Universal 2H/2C or 4H/2C HP
- + Event-Based™ Air Cleaning
- + Humidity or Ventilation
- + Wi-Fi touch screen



Model 8810

Temperature control.

- + Universal 2H/2C or 4H/2C HP
- + Event-Based™ Air Cleaning
- + Wi-Fi



Model 8800

Temperature control.

- + Universal 2H/2C or 4H/2C HP
- + Dual Fuel with Balance Points (HP Mode Only)
- + Temperature or Humidity Control (with 8082 External Sensor)
- + Touch screen
- + Serial Communications to Automation System

See product lineup on Page 6 for complete specifications.

Aprilaire SmartIAQ – Temperature,

Aprilaire **SmartIAQ** is an industry-leading design focused on consumer usability; providing users information when and where it's needed. Options can be selected that automatically control the indoor environment based on the needs of each individual consumer's home and family. And, when events occur in the home that affect indoor air quality, the Aprilaire exclusive Event-Based™ control options make managing and improving the air quality simple.



Industry-exclusive Features

- + Ability to control temperature and all IAQ equipment
- + Event-Based™ Air Cleaning and Fresh Air Ventilation
- + Automatic humidifier control with accurate ODT control points
- + Automatic dehumidifier control
- + Temperature overrides for instant comfort (“Heat Blast”) and maximum energy savings (“Away”)
- + All screens display the status of all IAQ and HVAC equipment
- + 3-Day weather forecast with pollen and mold levels
- + Features disabled from thermostat are automatically removed from the app
- + Informs homeowners on the benefits of IAQ control
- + “Product Not Installed” screen suggests additional IAQ products
- + Easy to identify and access “Help” screens ?

+ Easy-to-access navigation


The navigation bar showing all control options and status of equipment (on, off, idle) is visible from any screen. When first entering the app, the screen will always default to temperature.

Temperature

Not only do Wi-Fi thermostats give your customers the ability to modify their home's temperature from any mobile device, the Aprilaire scheduling and program


over-ride provide the usability needed to save money—without sacrificing comfort.

Air Purity, Humidity, Fresh Air Ventilation



Air Purity

The air customers breathe inside their homes can be the most polluted air they breathe all day. People who suffer from asthma and allergies will benefit from the ability to control air cleaning—especially with the unmatched simplicity of Aprilaire's exclusive Event-Based™ Air Cleaning feature.



Aprilaire 3-day weather forecast includes pollen and mold conditions to provide the information needed to determine when air cleaning is necessary.



Humidity


Too much or too little humidity can play a big role in your customers' comfort and health. Having the ability to verify and control humidity is required by many consumers.

Automatic Humidifier Control

Continuously monitors outdoor temperature while automatically adjusting the humidifier to provide optimum RH levels inside the home. Manual control is also available, if needed.

Automatic Dehumidifier Control

Automatically turns on a dedicated dehumidifier based on relative humidity. It couldn't be any simpler.



Fresh Air Ventilation

Fresh air ventilated from the outside is required in many new homes. That's why Aprilaire controls are designed to meet all ASHRAE 62.2—2010 requirements. Simply set the parameters and the control will ventilate the proper amount of air. Event-Based™ is also available for customers who want additional fresh air for circumstances such as cooking or parties.

Wi-Fi Connection That's Simple, Safe & Secure



Setup with your customer's home network is simple and secure, with the app being setup and controlled by the customer—not you. Aprilaire also provides setup support via phone at 1-800-334-6011 or online at My.Aprilaire.com

- 1 **DOWNLOAD** the Aprilaire Wi-Fi Thermostat App.
- 2 **REGISTER** your Aprilaire user account.
- 3 **CONNECT** the Wi-Fi thermostat to your home network.



✔ **Your Customers' Communication is Protected**

All communication between your customers' device and your customers' thermostat uses industry standard TLS (Transport Layer Security) 256 bit encryption.

✔ **Your Customers' Personal Data is Protected**

We only store personal data on our database servers. We use Amazon Web Services (AWS) to host our database servers. All personal data is encrypted using "Password salting and hashing" method with BCrypt algorithm. We will not share personal data with any third parties. We may use only non-personal data internally for analyzing overall usage of the app and equipment.

Find more detailed information at My.Aprilaire.com

Controls Designed for HVAC Contractors and Their Customers

Free Custom Imprinting

Aprilaire offers free imprinting of an HVAC contractor's logo on all battery covers to keep their business top of mind, for whenever HVAC needs should arise.

----- 1.75" x 0.625" Imprint Area

Imprint not available on Model 8840. Contractor information shows on screen.



Proud Partners with These Top Integration Specialists

 **WI-FI CONTROLLED**

SERIAL & HARD-WIRED





COMMUNICATING THERMOSTATS



Industry's most complete line of thermostats Available Soon! ▶

		8800 serial Programmable	8810	8820	Home Comfort Control™ 8830	Home Comfort Control™ 8840
USER INTERFACE	Screen Type	Backlit LCD	Backlit LCD	Backlit LCD	Backlit LCD	HD Color LCD
	Control Type	Touchscreen	Hard Button	Touchscreen	Touchscreen	Touchscreen
	Clock & Date Display (with Daylight Savings Adjustment)	●	●	●	●	●
	Adjustable Backlight Intensity	●		●	●	●
	Lockouts (Full, Timed, Limited)	F,T,L		F,T,L	F,T,L	F,T,L
COMMUNICATION	Automation Control Protocol	RS-485 (or RS-232)	Wi-Fi	Wi-Fi	Wi-Fi	Wi-Fi
	Cloud-based Control Protocol		Choose Cloud-based -or- Automation (LAN) mode			
TEMPERATURE CONTROL	Universal HVAC Control		"2H/2 Conv, 4H/2C HP"		"3H/3 Conv, 4H/2C HP"	
	Outdoor Temperature measurement and display	●	●	●	●	●
	Displays Outdoor Temperature and Humidity with Optional 8056				●	●
	Programmable	●	●	●	●	●
	Programmable Events Per Day	4 or 2	4	4	4	4
	Message Center with Real Language Set-up (allows display of custom messages from control system. For example... "Kitchen")	●		●	●	●
	Holds	●	●	●	●	●
	1/2 Degree Celsius Display and Control		●	●	●	●
	Auto Changeover with Deadband Adjustment (Both Heat & Cool Setpoints)	●	●	●	●	●
	Adjustable Differential (Allowed temperature drop between heat/Cool stages)	●	●	●	●	●
	Stage Rate (Engage additional stages to achieve setpoint)	●	●	●	●	●
	Progressive Recovery (Early start to meet setpoint at start of event)	●	●	●	●	●
	Heat Blast™ (Temporary heat boost button)			●	●	●
	Dual Fuel Kit (Allows switching between two equipment types)	●	●	●	●	●
	Balance Point Control (Allows optimization of heat pumps and Aux heat)	●	●	●	●	●
AIR CLEANING	Event-based™ Air Cleaning (On, Circ, 3hr & 24 Hour events)		●	●	●	●
HUMIDIFIER CONTROL	Automatic or Manual Control			●	●	●
DEHUMIDIFIER CONTROL	Whole Home Dehumidifier			●	●	●
DEHUMIDIFY W/AC	Controls dehumidifier on Air Conditioner to dehumidify			●	●	●
VENTILATION	Timed ventilation			●	●	●
	ASHRAE set up			●	●	●
	Temperature and Humidity Limits			●	●	●
	Notifies when active			●	●	●
CONFIGURATION	Wireless Outdoor Temperature / Humidity Sensor option (8056)				●	●
	Remote sensing via Support Modules (8081 & 8082)	●		●	●	●
	Monitor Temperature and Humidity via Support Modules	●		●	●	●
	Wi-Fi enrollment method		WAP Mode	WAP Mode	WAP Mode	WAP or Direct Entry
	All Power - 24 VAC	●	●	●	●	●
	Battery Backup	●				●
WARRANTY	Two-part design – 3 wires to living space				●	●
	Warranty	5-Year Warranty				
SERVICE	Installer Test Mode	●	●	●	●	●
	Reminders (Service, Water Panel, Dehumidifier, Air Cleaner, Ventilation)	S,W,D,A	W,A	S,W,D,A,V	S,W,D,A,V	S,W,D,A,V
	Return Air Temperature & Leaving Air Temperature sensors				●	●