

KLIKFIT™ ECONOMY LINE SET COVER



KlikFit™ Economy Line Set Cover is one of the most competitively priced line set cover products available today. Chock full of features, KlikFit™ gives you a great product at a competitive price.

KlikFit™ is low cost, flexible and quick and easy to install. The snap cover feature fits securely to the base and makes for easy assembly. The SpeediClip™ system uses an innovative rail molded into the back of the KlikFit™ channel. SpeediClips slides right onto the rail, and using a standard cable tie, attaches to and supports the line sets, drain line, and control cabling with just one person.

KlikFit™ fittings are a unique, one-piece design that easily snap onto the KlikFit™ channel and provide for custom tailored installations. All of the KlikFit™ components are molded from rigid, fire resistant PVC material. This yields a strong, durable, and rugged product that can take a beating. KlikFit™ is designed for

both outdoor and indoor installations. UV stabilizers compounded into the PVC protect KlikFit™ components from exposure to sunlight and keep the installation looking great.

KlikFit™ channel and component are also durable under a wide ambient temperature range (from -4F to 140F) permitting installation in a wide variety of climates. KlikFit™ system components are easily paintable to match any décor and are the perfect answer for economical installations.

CATALOG NO.	DESCRIPTION	ORDER UOM	ORDER MULT.	LIST PRICE
229-CP3	KlikFit™ 3 inch union coupling	EA	10	\$5.44
229-CP4	KlikFit™ 4 inch union coupling	EA	10	\$6.92
229-D3	KlikFit™ 3 inch channel	EA	8	\$41.60
229-D4	KlikFit™ 4 inch channel	EA	4	\$54.96
229-DC3	KlikFit™ 3 inch cap	EA	10	\$8.92
229-DC4	KlikFit™ 4 inch cap	EA	10	\$13.48
229-EB3	KlikFit™ 3 inch 90 degree inside elbow	EA	10	\$9.16
229-EB4	KlikFit™ 4 inch 90 degree inside elbow	EA	10	\$12.52
229-EIN3	KlikFit™ 3 inch 90 degree outside elbow	EA	10	\$9.16
229-EIN4	KlikFit™ 4 inch 90 degree outside elbow	EA	10	\$12.52
229-FB3	KlikFit™ 3 inch 90 degree flat bend	EA	10	\$11.64
229-FB4	KlikFit™ 4 inch 90 degree flat bend	EA	10	\$19.40
229-FR3	KlikFit™ 3 inch flat wall escutcheon	EA	10	\$11.28
229-FR4	KlikFit™ 4 inch flat wall escutcheon	EA	10	\$16.68
229-TC34	KlikFit™ (3 x 4) reducer coupling	EA	10	\$8.36
229-TJ3	KlikFit™ 3 inch T-joint	EA	10	\$22.92
229-TJ4	KlikFit™ 4 inch T-joint	EA	10	\$32.40
229-WC3	KlikFit™ 3 inch wall penetration cover	EA	10	\$14.56
229-WC4	KlikFit™ 4 inch wall penetration cover	EA	10	\$20.36