

WhisperControl

Specification Submittal Data / Panasonic Ventilation Fan

FV-WCCS1-W (White)

FV-WCCS1-A (Almond)

— FAN Only

Condensation Sensor – 3 controls in 1

Humidity – Countdown Timer – Manual On/Off Control

Humidity Control – Automatically turns on exhaust fan to control humidity

Countdown Timer – Manually turning the fan on initiates a 30 minute countdown cycle

Manual On/Off Control – Push the switch for manual fan operation

Includes matching wall plate



Product Specifications	
Ground	Grounding
Feature	Blue Led Light When On
Amperage	15
Maximum Fan Load	1/8 hp or 3 Amps
Voltage	120 Volts
Terminations	6" Leads
Connections (Copper Wire Connections)	Use #14 or #12
Max Fluorescent Light Load	N/A
Standards and Classifications	UL/CSA Listed
Warranty	1 Year Limited

FV-WCCS2-W (White)

FV-WCCS2-A (Almond)

— FAN/LIGHT

Condensation Sensor – 3 controls in 1

Humidity – Countdown Timer – Manual On/Off/ Light Control

Humidity Control – Automatically turns on exhaust fan to control humidity

Countdown Timer – Manually turning the fan on initiates a 30 minute countdown cycle

Manual On/Off Control – Push the switch for manual fan operation

Includes matching wall plate



Product Specifications	
Ground	Grounding
Feature	Blue Led Light When On
Amperage	15
Maximum Fan Load	1/8 hp or 3 Amps
Voltage	120 Volts C21
Connections (Copper Wire Connections)	Use #14 or #12
Max Fluorescent Light Load	400 Watt
Standards and Classifications	UL/CSA Listed
Warranty	1 Year Limited

For complete Installation Instructions visit
www.panasonic.com/building

Model	Quantity	Comments	Project:
			Location:
			Architect:
			Engineer:
			Contractor:
			Submitted by:
			Date:

Panasonic Home and Environment Company
 Division of Panasonic Corporation of North America
 One Panasonic Way
 Secaucus, NJ 07094
www.panasonic.com/building



Panasonic ideas for life

WhisperControl

Specification Submittal Data / Panasonic Ventilation Fan

FV-WCSW11-W (White) / FV-WCSW11-A (Almond)

One Function Control

On/Off switch with pilot light – Fits single-gang box
Includes matching wall plate



Product Specifications	
Ground	Self Grounding
Feature	Pilot Light – Illuminated ON – Req. Neutral
Amperage	20 Amp
Voltage	120 Volt
HP Rating	1HP-120V
Terminations	Back & Side Wire
Standards & Certifications	UL/CSA Listed
Warranty	10 Year Limited

FV-WCSW21-W (White) / FV-WCSW21-A (Almond)

Two Function Control

2 independent rocker switches – Fits single-gang box
Includes matching wall plate



Product Specifications	
Ground	Grounding
Feature	Single Pole/ Single Pole
Amperage	15 Amp
Voltage	120 Volt
Termination	Quickwire Push-In, Back & Side Wire
Standards & Certifications	UL/CSA Listed
Warranty	2 Year Limited

FV-WCSW31-W (White) / FV-WCSW31-A (Almond)

Three Function Control

3 independent rocker switches – Fits single-gang box
Includes matching wall plate



Product Specifications	
Ground	Grounding
Feature	Single Pole/ Single Pole/ Single Pole
Amperage	15 Amp
Voltage	120 Volt
Termination	Quickwire Push-In, Back & Side Wire
Standards & Certifications	UL/CSA Listed
Warranty	2 Year Limited

FV-WCSW41-W (White only)

Four Function Control

3 independent rocker switches – Fits single-gang box
Designed for model FV-11VHL2 Heater/Fan/Light/Night-Light
Includes matching wall plate



Product Specifications	
Ground	Grounding
Feature	Single pole/double throw on-off-on top switch, two single pole on-off switches
Individual Switch Amperage	15 Amp
Total Switch Amperage	20 Amp
Voltage	120 Volt
Termination	Quickwire Push-In, Back & Side Wire
Standards & Certifications	UL/CSA
Warranty	2 Year Limited

FV-WCD01-W (White) / FV-WCD01-A (Almond)

Preset Countdown Delay Off Timer

Preset for 10-20-30 or 60 minute intervals

Fits single-gang box

LED light indicates countdown time elapsed and last LED flashes two minutes until OFF warning

Simple press and hold override timer function; hold down the button you want until LED light indicates it is on

Includes matching wall plate



Product Specifications	
Ground	Grounding
Feature	Req. Neutral
Amperage	20 Amp
Voltage	120 Volt
HP Rating	1HP-120V
Termination	6" Leads
Standards & Certifications	UL/CSA Listed
Warranty	5 Year Limited

For complete Installation Instructions visit

www.panasonic.com/building

Model	Quantity	Comments	Project:
			Location:
			Architect:
			Engineer:
			Contractor:
			Submitted by:
			Date:

Panasonic Home and Environment Company
Division of Panasonic Corporation of North America
One Panasonic Way
Secaucus, NJ 07094

www.panasonic.com/building



Panasonic ideas for life