# Shut-Off *freedom* Swivel-Flange®

Taco's new Shut-Off *freedow* Swivel-Flange® combines a full-port, ball valve and companion flange to isolate system circulators for easy removal and service, without draining the system. Simplify your next  $00^{\circ}$  circulator installation while saving material and labor costs. Solid brass uni-body construction, available in 1/2" – 1-1/2" NPT or Sweat connections. The Swivel-Flange provides easier installation and positioning of the pump and lever handle in the most convenient location.







©Taco Catalog # 100-56

Supersedes: 10/22/08

Effective Date: 08/02/11

Printed in USA

Submittal Data # 101-132 Supersedes: 10/22/08

# Submittal Data Information Shut-Off *freedom* Swivel-Flange $^{\circledR}$

Effective: 08/02/11

#### **Features**

- Easy 1/4-turn Open/Close Operation
- Positive Shut-off, Leak Free Design
- Swivel Flange allows 360° rotation
- Solid Brass Construction
- Chrome/Brass Valve Ball
- High Quality Teflon® Seats
- Full Port Ball Valve For Unrestricted Flow
- 150# WP
- Available Sizes: 1/2" 1-1/2" NPT

1/2" — 1-1/2" Sweat

• Includes Bolts and Nuts

#### **Materials of Construction**

Valve Body: Solid Brass

Valve Ball: Chrome Plated Brass

Flange: Epoxy Powder Coated Steel

Packing Seal: Teflon® 1
Valve Seat : Teflon® 2
Valve Stem: Brass

Handle: Chrome Plated Steel/Vinyl Cover

#### **Operating Data**

Maximum WP = 150 psi

Maximum Operating Temp: 240°F (115C°)

## **Shut-off Flanges for Taco® Circulator Models**

Size	Model # NPT	Model # Sweat	Taco* Circulator Model #		
1/2"	SF-050T	SF-050S	006,005,007,008,009,0010		
3/4"	SF-075T	SF-075S	0011,0013,0014, 00R, 0015		
1"	SF-100T	SF-100S	110,111,112,113		
1-1/4"	SF-125T	SF-125S	2400-10,2400-20, 2400-45,2400-50		
1-1/2"	SF-150T	SF-150S			
1-1/4"	SF-125T-0012	SF-125S-0012	0012-F4		
1-1/2"	SF-150T-0012	SF-150S-0012	2400-30, 2400-40		

#### **Application**


The Taco Shut-Off *freedom* Swivel-Flange® is a combination full port shut-off ball valve and swivel companion flange for most Taco circulators. The simple quarter turn, lever handle operation allows for easy isolation, removal and service of circulators without draining the system. Each flange set includes bolts and nuts. Available in sizes 1/2" to 1-1/2", NPT and Sweat connections, rated for 240°F, 150# WP.

## **Dimensions & Weights**

Model #	A	В	С	D	Е	F	G	Wt./Set
1 lodel #	Size	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	lbs. (kg)
SF-050T	1/2" NPT	2 (51)	2 (51)	4-1/8 (105)	2-3/4 (70)	3-7/8 (98)	3-1/8 (79)	2.5 (1.1)
SF-075T	3/4" NPT	2-1/4 (57)	2 (51)	4-1/8 (105)	2-3/4 (70)	3-7/8 (98)	3-1/8 (79)	3.0 (1.4)
SF-100T	I" NPT	2-1/2 (64)	2-1/2 (64)	4-1/8 (105)	2-3/4 (70)	4-1/2 (114)	3-1/8 (79)	3.5 (1.6)
SF-125T	I-1/4" NPT	2-3/4 (70)	2-7/8 (73)	4-1/8 (105)	2-3/4 (70)	4-1/2 (114)	3-1/8 (79)	4.0 (1.8)
SF-150T	I-1/2" NPT	3-7/8 (98)	3-1/2 (89)	4-1/8 (105)	2-3/4 (70)	5-1/2 (140)	3-1/8 (79)	5.2 (2.3)
SF-125T-0012	I-1/4" NPT	2-3/4 (70)	2-7/8 (73)	4-1/2 (114)	3 (76)	4-1/2 (114)	3-1/2 (89)	4.7 (2.1)
SF-150T-0012	I-1/2" NPT	3-7/8 (98)	3-1/2 (89)	4-1/2 (114)	3 (76)	5-1/2 (140)	3-1/2 (89)	6.9 (3.1)
SF-050S	1/2" Swt.	2 (51)	2 (51)	4-1/8 (105)	2-3/4 (70)	3-7/8 (98)	3-1/8 (79)	2.5 (1.1)
SF-075S	3/4" Swt.	2-1/2 (64)	2 (51)	4-1/8 (105)	2-3/4 (70)	3-7/8 (98)	3-1/8 (79)	3.0 (1.4)
SF-100S	I" Swt.	2-3/4 (70)	2-1/2 (64)	4-1/8 (105)	2-3/4 (70)	4-1/2 (114)	3-1/8 (79)	3.5 (1.6)
SF-125S	I-1/4" Swt.	3 (76)	2-3/4 (70)	4-1/8 (105)	2-3/4 (70)	4-1/2 (114)	3-1/8 (79)	4.0 (1.8)
SF-150S	I-1/2" Swt.	4-1/8 (105)	3-1/2 (89)	4-1/8 (105)	2-3/4 (70)	5-1/2 (140)	3-1/8 (79)	6.0 (2.7)
SF-125S-0012	I-I/4" Swt.	3 (76)	2-3/4 (70)	4-1/2 (114)	3 (76)	4-1/2 (114)	3-1/2 (89)	4.7 (2.1)
SF-150S-0012	I-1/2" Swt.	4-1/8 (105)	3-1/2 (89)	4-1/2 (114)	3 (76)	5-1/2 (140)	3-1/2 (89)	6.9 (3.1)

Dimensions and weights are approximate.







Teflon is a Trademark of El Dupont de Nemours, Inc.