


Ox Box™

NEW

Gas Outlet Box



- **ACCESSIBLE**

1/4-turn ball valve for easy, secure, accessible operation

- **VERSATILE**

Box is available for 1/2" or 3/4" iron-pipe applications or 1/2" CSST applications in both standard and fire-rated products

- **STRENGTH**

Recessed box is made of high-impact ABS providing the strongest finished installation for all gas appliance needs

- **CERTIFIED**

Valve has CSA certification to ANSI Z21.15-1997 / CGA 9.1-M97



Supply • Drainage • Support • Testing • Specialties • Tools • Access

Sioux Chief 
MANUFACTURING SINCE 1957

Gas Ox Box Benefits

- Frame Extension (696-EX): extends box face for installations thicker than ½" drywall
- Solid Frame Insert (696-SC): can be cut as desired to fit around gas lines for flush cover
- Box/frame can be painted or wallpapered and has a modern beveled frame
- Iron Pipe test plug included in each gas box installation kit.
- Residential, commercial, and industrial direct connect application include: gas range, wall heater, water heater, garage heater supply, furnaces, laundry washers and dryers.

Additional Ox Box Outlet Boxes for Washing Machine and Ice Maker



Additional Sioux Chief Products

Tools and Gas Products



Tools

Heavy duty pipe wrench and adjustable pliers



Gas Products

Gas ball valves, angled and straight log lighter valves, log lighter bars

Installations

Before installing: Make sure valve and gas source are turned off and line is purged before installation.

- 1 Set Ox Box supply box directly to stud and/or on support bracket.
- 2 Insert supplied valve adapter through hole in the box and hand tighten locknut.
- 3 Apply pipe thread sealant to male threads and tighten supply piping. Tighten locknut with a wrench. For CSST, follow applicable manufacturer's installation instructions for adapter.
- 4 Apply pipe thread sealant to bottom of valve and tighten. Do not overtighten.
- 5 Check all connections for leaks using leak detector.
- 6 Turn off gas supply and connect appliance according to manufacturers instructions.

Note: Use appropriate and code mandated pipe protection and insulation. Consult all local and applicable building/gas codes prior to and during installation and testing. Use box for indoor applications only. Keep flame or other combustion sources away during installation.



Item No.	Connection	Pkg	Min. Qty	Case Qty	List Price
GAS OX BOX					
696-1021GF	½" NPT valve and adapter for iron pipe, bagged	B	6	6	28.99 EA
696-1031GF	¾" NPT valve and adapter for iron pipe, bagged	B	6	6	32.40 EA
696-1020GF	½" FIP valve for CSST connection, bagged	B	6	6	26.00 EA
FIRE-RATED GAS OX BOX					
696R1021GF	½" NPT valve and adapter for iron pipe, bagged	B	6	6	73.21 EA
696R1031GF	¾" NPT valve and adapter for iron pipe, bagged	B	6	6	76.62 EA
696R1020GF	½" FIP valve for CSST connection, bagged	B	6	6	70.22 EA
OX BOX ACCESSORIES					
696-EX	Frame extension	B	10	10	3.25 EA
696-SC	Solid frame insert	B	10	10	4.00 EA

Packaging Codes || B: bulk

DISTRIBUTED BY

24110 South Peculiar Drive
Peculiar, Missouri 64078
tel: 1-800-821-3944
fax: 1-800-758-5950
www.siouxchief.com

