

choosing Pro1.

This manual covers the following models: • T601

**Congratulations on purchasing a new thermostat.** This thermostat was designed to the highest reliability and ease of use standards. Thank you for



# Caution

Equipment damage hazard: Do not operate the cooling system if the outdoor temperature is below 50° F (10° C) to prevent possible compressor damage.

Table of Contents	Page
Thermostat Quick Reference	2
Thermostat Operation	3
Contact Us	4
Warranty Registration	4

# **Need Help?**

For assistance with this product please visit http://www.pro1iaq.com or call Pro1 Customer Care toll-free at 888-Pro1iaq (776-1427) during normal business hours (Mon-Fri 9 AM - 6 PM Eastern)

Una versión española de este manual puede ser descargada en www.pro1iaq.com

# OPERA THERMOSTAT QUICK REFERENCE

### Getting to know your thermostat





Indicates the current **Room Temperature** 

**ON** is shown when there is a call for heat or cool

**HEAT, OFF** or **COOL** is shown per current system switch settings

Low Battery Indicator: Replace batteries when indicator is shown

Swing Adjust Icon: Shown when temperature swing is being adjusted

2) Temperature Setpoint Dial

3) Fan Switch

4) System Switch

5) Easy Change Battery Door



#### Important:

The low battery indicator is displayed when the AA battery power is low. If the user fails to replace the battery within 21 days, the thermostat display will only show the low battery indicator as a final warning before the thermostat becomes inoperable.

#### **Battery door information**



# Easy to use controls





#### **Caution:**

When the battery icon appears replace your AA batteries immediately. Failure to do so may result in your heating & cooling system becoming inoperable.

#### (1) LCD Display:

See page 2 for details about this display read out and icons.

	-
1	• .
ι.	~
~	_

#### 2) Temperature Setpoint Dial:

Turn the adjustment knob to the desired room temperature. There is a marker on the knob that points to the current setting.

#### (3) Fan Switch:

Fan Switch: Select ON or All

Select **ON** or **AUTO**. **ON** will run the fan continuously. **AUTO** will cycle the fan on only when the heating or cooling system is on.

#### (4) System Switch:

Selects the operation mode of your HVAC system. Selecting **HEAT** turns on the heat mode. Selecting **COOL** turns on the air conditioning mode. Selecting **OFF** turns both heating and cooling off.

#### **Contact Us Information**

#### **Pro1 IAQ Inc.**

1111 S. Glenstone Suite 2-100 Springfield, MO 65804

Toll-free: 1-888-Pro1iaq (776-1427) Toll Number (Outside the USA): 330-821-3600 Web: http://www.pro1iaq.com Hours of Operation: Monday - Friday 9 AM - 6 PM Eastern

# Warranty Registration:

Your new Pro1 thermostat has a 5 year limited warranty. You must register your warranty within 60 days of installation. You can register your new thermostat in 2 ways.

① Go to www.pro1iaq.com, select warranty registration and fill out a short registration form.

- or -

② Complete the form below and mail it to the address shown.

# **Pro1 IAQ Warranty Registration:**

Name:	Thermostat Model:	
Address:	Date Installed:	
City:	Complete form and mail to:	
State:	Pro1 IAQ Inc.	
	1111 S. Glenstone	
Zip:	Suite 2-100	
	Springfield, MO 65804	