



SUPPLY AND RETURN BALL VALVES/ MANIFOLD ADAPTERS

SELL SHEET



Uponor Supply and Return Ball Valves

Uponor's Supply and Return Ball Valves are designed with 1¼" BSP (R32) connections to maximize flow capabilities for the following Uponor radiant heating and cooling manifolds.

- TruFLOW™ Jr. Manifold
- TruFLOW Classic Manifold
- Engineered Polymer (EP) Heating Manifold

All ball valves come in a set of two for supply and return lines and feature a union nut for fast, easy commissioning of a radiant system.


Choose from our complete ball valve offering to effectively meet any application need, and feel confident knowing Uponor backs all its ball valves with a 2-year limited warranty.

Part No.	Part Description	Filter	Temp. Gauge	Features
A2631250	Manifold Supply and Return Ball Valves with Filter and Temperature Gauge, set of 2	✓	✓	Internal filter and temperature gauge monitors supply and return temperatures
NEW A2631251	Manifold Supply and Return Ball Valves with Temperature Gauge, set of 2		✓	Temperature gauge monitors supply and return temperatures
NEW A2631252	Manifold Supply and Return Ball Valves, set of 2			Cost-effective option

Uponor Manifold Adapters

Uponor's complete line of manifold adapters offer the fastest, most reliable method for connecting Wirsbo hePEX™ tubing or copper pipe to TruFLOW™ and Engineered Polymer (EP) Heating Manifolds.


- Easily adjust piping orientation
- Straight and elbow adapters feature ProPEX® F1960 expansion fittings for fast, easy connections and maximum flow
- Brass manifold adapters offer copper sweat connection
- Available for pipe sizes from ¾" to 1½"



ProPEX Manifold Elbow Adapter



ProPEX Manifold Straight Adapter



Brass Manifold Combination Adapter

Part No.	Part Description	Size			
		¾"	1"	1¼"	1½"
Q4143275	ProPEX Manifold Straight Adapter, R32 x ¾" ProPEX	✓			
Q4143210	ProPEX Manifold Straight Adapter, R32 x 1" ProPEX		✓		
NEW Q4143213	ProPEX Manifold Straight Adapter, R32 x 1¼" ProPEX			✓	
NEW Q4143215	ProPEX Manifold Straight Adapter, R32 x 1½" ProPEX				✓
Q4153275	ProPEX Manifold Elbow Adapter, R32 x ¾" ProPEX	✓			
Q4153210	ProPEX Manifold Elbow Adapter, R32 x 1" ProPEX		✓		
NEW Q4153213	ProPEX Manifold Elbow Adapter, R32 x 1¼" ProPEX			✓	
NEW Q4153215	ProPEX Manifold Elbow Adapter, R32 x 1½" ProPEX				✓
A4143210	Brass Manifold Adapter, R32 x ¾" Adapter or 1" Fitting Adapter	✓	✓		
A4133210	Brass Manifold Adapter, R32 x 1" Adapter or 1¼" Fitting Adapter		✓	✓	
NEW A4123215	Brass Manifold Adapter, R32 x 1¼" Adapter or 1½" Fitting Adapter			✓	✓

Uponor, Inc.
 5925 148th Street West
 Apple Valley, MN 55124 USA
 Tel: 800.321.4739
 Fax: 952.891.2008

Uponor Ltd.
 2000 Argentia Rd., Plaza 1, Ste. 200
 Mississauga, ON L5N 1W1 CANADA
 Tel: 888.994.7726
 Fax: 800.638.9517

uponor

www.uponorpro.com