

VisionPRO® 8000 Series Product Comparison



| FEATURES | PRODUCT | | | |
|---|--|---|---|---|
| | VisionPRO® 8000 Series | White-Rodgers® 1F95-1291 | Aprilaire® 8600 | Pro1® IAQ T955 |
| Touchscreen User Interface | Yes | Yes | Yes | Yes |
| Viewable Display Size | 10 sq. in. | 12 sq. in. | 10.3 sq. in. | 13 sq. in. |
| Real-Time Clock | Yes (with daylight savings) | Yes (with daylight savings) | No | No |
| Dual-Powered | Yes (battery and/or 24 VAC) | Yes (battery and/or 24 VAC) | Yes (battery and/or 24 VAC) | Yes (battery and/or 24 VAC) |
| Applications | Gas, oil, electric, HP, hot water, steam, multistage, 750mV, geothermal | Gas, oil, electric, HP, hot water, steam, multistage, 750mV | Gas, oil, electric, HP, hot water, steam, multistage, 750mV | Gas, oil, electric, HP, hot water, steam, multistage, 750mV |
| Installation Options | Completely wireless or 2-wire with Equipment Interface Module (EIM); or wired with power by battery and/or 24 VAC | Wired with power by battery and/or 24 VAC | Wired with power by battery and/or 24 VAC | Wired with power by battery and/or 24 VAC |
| Stages | Up to 3H/2C heat pump, up to 2H/2C conventional (up to 4H/2C heat pump, up to 3H/2C conventional with EIM) | Up to 4H/2C heat pump, Up to 2H/2C conventional | Up to 4H/2C heat pump, Up to 2H/2C conventional | Up to 3H/2C heat pump, Up to 2H/2C conventional |
| Meets Commercial Code and Title 24 Compliance | Yes | No | No | No |
| Backlit Display | Yes (continuous or on-demand) | Yes (continuous or on-demand) | Yes (continuous or on-demand) | Yes (continuous or on-demand) |
| Indoor Air Quality Support | Humidification, dehumidification, ventilation (with EIM) | Humidification, dehumidification | No | No |
| Wireless Technology | RedLINK™ | No | No | No |
| Wireless Accessories Available | Yes (Outdoor air sensor, indoor air sensor, entry/exit remote, vent and filter boost remote, portable comfort control, RedLINK internet gateway) | No | No | No |
| Remote Connectivity | Yes (Apple®/Android™ apps and internet enabled devices) | No | No | No |
| Message Center | Yes (2-line) | No | Yes (2-line) | No |
| Copy Installer Setup from One Thermostat to Another | Yes | No | No | No |
| On-Screen Dealer Information | Yes | No | No | No |
| Data Logs Available | Yes (alerts and user interaction) | No | No | No |
| Alerts and Reminders | Yes (standard and customizable) | Yes (standard) | Yes (standard) | Yes (standard) |
| Temperature Range Stops | Yes | Yes | No | Yes |
| Keypad Lockout | Yes (partial and full) | Yes (partial and full) | Yes (partial and full) | Yes (partial and full) |
| Private Label Program | Yes | Yes | No | Yes |
| Warranty | 5 years | 5 years | 5 years | 5 years |