

Wi-Fi 9000® Color Touchscreen Product Comparison



FEATURES	PRODUCT			
	Wi-Fi 9000	Venstar® ColorTouch™ T5800	ecobee Smart	nest® 2nd Generation
Full-Color Touchscreen Graphical Display	Yes	Yes	Yes	No
Changeable Background Color Themes	Yes	Yes	No	No
Frame Color Options	White front with white sides	White, black, silver, wood grain	White, optional GelaSkins	No
Viewable Display Size	8 sq. in.	8 sq. in.	5.7 sq. in.	2.4 sq. in.
Internet Time Sync	Yes (with daylight savings)	Yes (with daylight savings)	Yes (with daylight savings)	Yes (with daylight savings)
Power Method	24 VAC hardwired	24 VAC hardwired	24 VAC hardwired	24 VAC hardwired or rechargeable Li-ion battery
Applications	Gas, oil, electric, HP, hot water, steam, multistage	Gas, oil, electric, HP, hot water, steam, multistage, 750mV	Gas, oil, electric, HP, hot water, steam, multistage, 750mV, geothermal	Gas, oil, electric, HP, hot water, steam, multistage, 750mV, geothermal
Backlit Display	Yes (continuous, adjustable intensity)	Yes (continuous, adjustable intensity)	Yes (continuous, adjustable intensity)	Yes (on-demand)
Stages	Up to 3H/2C heat pump, Up to 2H/2C conventional	Up to 4H/2C heat pump, Up to 3H/2C conventional	Up to 4H/2C heat pump, Up to 3H/2C conventional	Up to 3H/2C heat pump, Up to 2H/2C conventional
Dry Contact Alerts	No	No	Yes	No
Indoor Air Quality Support	No	No	Humidification, dehumidification, ventilation	Humidification, dehumidification
Wireless Technology	Wi-Fi	Wi-Fi (skyport adapter sold separately)	Wi-Fi	Wi-Fi, ZigBee®
Remote Connectivity	Yes (Apple®/Android™ apps and internet-enabled devices)	Yes (Apple/Android apps and internet-enabled devices)	Yes (Apple/Android apps and internet-enabled devices)	Yes (Apple/Android apps and internet-enabled devices)
Plain Language Setup	Yes	Yes	Yes	Yes
Copy Installer Setup from One Thermostat to Another	No	Yes	No	No
On-Screen Dealer Information	No	Yes (dealer logo and information)	Yes (dealer logo and information)	No
Data Logs Available	No	Yes (performance)	Yes (performance)	Yes (performance)
Alerts and Reminders	Yes (standard)	Yes (standard)	Yes (standard)	Yes (standard)
Temperature Range Stops	Yes	Yes	Yes	Yes
Keypad Lockout	Yes (partial and full)	Yes (partial and full)	Yes (partial and full)	Yes (partial)
Multiple Languages	Yes (English, French and Spanish)	Yes (English, French and Spanish)	No	Yes (English, French and Spanish)
Warranty	5 years	1 year	3 years	2 years