

Robertshaw®

9420

DIGITAL
THERMOSTAT

new series!



HEAT PUMP

2 Heat / 2 Cool

Incredible Digital

When it comes to non-programmable temperature control, we listened to the experts—YOU! Our new 9420 is the next evolution in digital thermostats. The LCD display is clearly one of the largest in the industry, up to 80% larger than competitive models. Plus, the display is back lit, making it even easier to read in a dark room.

This model is loaded with enhanced features. The 9420 comes with permanent winter and summer setpoint memory, allowing you to save both heating and cooling temperature settings. This eliminates temperature adjustments when switching systems for seasonal requirements. And our fully adjustable differential control provides increased comfort for your customers. The 9420 is compatible with all standard 24 Volt AC multi-stage heat pump systems.

When you select a Robertshaw thermostat, you've made the choice of an industry partner that's been making quality products for 100 years. Come home to affordable comfort. Come home to RobertshawSM.

Features and Benefits

Larger Back Lit Display

Makes viewing and setting the temperature easy and accurate.

Winter and Summer Permanent Setpoint Memory

Allows you to save both heating and cooling temperature settings.

Automatic Compressor Short Cycle Protection

A system safeguard. Reduces wear and tear of HVAC equipment.

Worry-Free Memory Storage

Even during power outages, the thermostat maintains setpoint and programmed parameters.

Adjustable 1st and 2nd Stage Temperature Differential

Maintains optimal customer comfort.

O & B Terminals

Greater system flexibility, zoning compatible.

Zone System Compatible

In zoning applications where temperature is precisely controlled, the thermostat acts as a sensor within the system.

Quick Wire Terminal Block

Fast and easy installation. Uses sturdy wire clamps — no wrap-around of screws.

Toll-Free Assistance

Toll-Free Technical Service number printed right on the thermostat provides immediate assistance.



Technical service available:

1-800-445-8299

M-F 7:00 a.m. - 5:30 p.m. CST



Robertshaw®

9420

DIGITAL
THERMOSTAT


new series!



HEAT PUMP

Terminal Designations

2 Heat / 2 Cool



THE ROBERTSHAW 9420 REPLACES:

Robertshaw	9520
White-Rodgers Company*	1F89-211
Honeywell, Inc.*	T8411R

* Verify specific application requirements before substitution.

Specifications

Electrical rating: 24 Volt AC (18-30 VAC)

1 amp maximum load per terminal

3 amp total maximum load

(all terminals combined)

Temperature control range: 45° - 90°F (7° - 32°C)

Accuracy: +/-1°F (+/-0.5°C)

Power: 24 VAC

System configurations: Multi-stage heat pump systems - two stage heat, two stage cool

Terminations: C, L, R, Y2, Y1, E, G, W2, O, B

Shipping Information

Indiv. Ctn. Dim.: 6.75" x 4.375" x 1.625"

Master Ctn. Qty.: 6

Master Ctn. Dim.: 9.25" x 5.625" x 7.625"

Master Ctn. Cu. Ft.: .23

Master Ctn. Wt.: 4.0 lbs.

Max. Pallet Qty.: 1170

Max. Pallet Dim.: 40" x 48" x 48"

Max. Pallet Cu. Ft.: 53.33

Max. Pallet Wt.: 835 lbs.

Other Two Stage Heat, Two Stage Cool Thermostats

9620: Programmable, 2 Heat / 2 Cool, HP

9720i: Deluxe Programmable, 2 Heat / 2 Cool, HP

invensys®

Controls Americas
515 South Promenade Avenue
Corona California 92879-1736 USA
Telephone +1 800 951 5526 Facsimile +1 630 260 7299
iccacustomerservice@invensys.com
www.icca.invensys.com
©2005 Controls Americas 1/05 - #150-1690C

Distributed by: