

"THERMOSTATIC"

MICRO PROCESSING TEMPERATURE CONTROL

Instant Comfort...Endless Savings

ELECTRIC TANKLESS WATER HEATERS

9/06

MODELS:

	Thermostatic			
	Options	Volts	kW	Amps
EX2412T	S,FS,P,DR	120V	2.4kW	20A
EX3012T	S,FS,P,DR	120V	3.0kW	25A
EX3512T	S,FS,P,DR	120V	3.5kW	29A
EX48T	EE,ML,S,P,FS,DR	240V*	4.8kW	20A
EX55T	EE,ML,S,P,FS,DR	240V*	5.5kW	23A
EX65T	EE,ML,S,P,FS,DR	240V*	6.5kW	27A
EX75T	EE,ML,S,P,FS,DR	240V*	7.5kW	32A
EX95T	EE,ML,S,P,FS,DR	240V*	9.5kW	40A
EX8208T	EE,ML,S,P,FS,DR	208V	8.3kW	40A
EX60T	EE,ML,S,P,FS,DR	277V	6.0kW	22A
EX80T	EE,ML,S,P,FS,DR	277V	8.0kW	29A
EX90T	EE,ML,S,P,FS,DR	277V	9.0kW	33A
EX100T	EE,ML,S,P,FS,DR	277V	10.0kW	36A

^{*}Units can be used at 208V with 25% reduced output.

SPECIFICATION OPTIONS

- □ EE = Emergency Eyewash "Tepid Water" ANSI Z358.1
 □ ML = Multiple Lavs (5.5kW 10kW)
 □ S = Sanitation Setting 180°

- □ P = Photo Setting temperatures ambient to 100°
- ☐ FS = Factory set temperature (ambient to 180°)
- ☐ DR = External temperature control
 - LED temperature display (see "Digital Readout" spec sheet)

APPLICATIONS:

- Dishwashers, Boosters (to 180°F) (S)
- Single and multiple handwash sinks maintain precise outlet temp for one, two, or three sinks code compliant (.5 GPM @ 105°F)(ML)
- Multi Station Modular Sinks
- Emergency eye wash fountains (EE)
- Metering and sensor faucet compatible
- Low volume shower handset (.7-2 GPM)
- Photo Processing (P)
- Schools/Hospitals/Nursing Homes/Laboratories
- Eliminate wait for hot water, long pipe runs
- Maintains accurate temperature continuously +/- 1°F





Emergency Eye/Face Wash **Fountains**



Multiple Sinks



Low Volume **Hand Shower** (.7 GPM - 2 GPM)



Boosters for Sanitation





ADVANCED TECHNOLOGY • HIGHEST EFFICIENCY • DESIGNED FOR DURABILITY

QUALITY FEATURES

- Fully Adjustable Temperature Range between 100-140°. Special settings of higher or lower range available upon request. (see spec options)
- Eliminate Costly Mixing Valves.
- On Demand Hot Water no delay.
- Continuous Hot Water no storage capacity to run out.
- Reduces Installation Cost and Material no T & P relief valve needed (check local codes).
- Easy Installation only one cold or hot water line need be brought to installation - integral compression fittings for 1/2" pipe (5/8" OD) on bottom (no sweat connections).
- Cut Energy Waste flow switch activates heater only on demand (no standby heat loss) - 99% efficient.
- Sophisticated microprocessing temperature control (+/- 1°F).

- Prevents Legionella Bacteria Growth.
- Meets ANSI Z358.1 Tepid Water Requirements
- Anti-scald Protection. Reduce wide temperature fluctuation.
- Reduces Calcification, Liming and Sedimentation.
- Complies with Handicap Requirements.
- Compact Size dimensions 10.75"x5.25"x2.87" weight 3 lbs.
- Field Serviceable Element replaceable cartridge element (1 year warranty).
- Warranty Full Factory Warranty Heaters are guaranteed against failure due to leaks of "Heater Body/Element Assembly" for a period of FIVE YEARS.
- High Temperature Limit Switch protects against element burn out, with reset button

THERMOSTAT OPTIONS

- Standard unit has fully adjustable thermostat 100-140°
- Higher temperature available up to 180°F upon request. (S)
- "Digital Readout", external temperature adjustment range 2.4 kW - 32 kW. (see "Digital Readout" spec sheet) (DR)
- Factory set, nonadjustable thermostat available. (FS)
- Photoprocessing unit lower temperature range ambient to 100°. (P)
- "Tepid" warm water (60° 95°F) for Emergency Eye wash fountains available. Complies with ANSI Z358.1 (EE)

THERMOSTAT ACCURACY

- Thermostatic feature maintains +/- 1°F accuracy.
- Achieves full, pre-selected outlet temperature within 10 seconds after activation.
- Maintains consistent temperature.

SUGGESTED SPECIFICATION

Tankless Water Heater shall be an Eemax Thermostatic Model, with microprocessing temperature control capable of maintaining outlet temperature of +/- 1°F accuracy,

	, with			kW.
model #		kW rating		
vac, and _	to heat		GPM	@ a
voltage	amperage			

___ degrees F. Unit shall have ABS-UL temperature rise of 94Vo rated cover. Element shall be replaceable cartridge insert. Unit shall have replaceable filter in the inlet connector. Element shall be iron free, Nickel Chrome material. Heater shall be fitted with 1/2" pipe compression nuts (5%" OD) or 3/8" sleeves, to eliminate need for soldering. Maximum operating pressure of 150 PSI. Hot water storage tanks prohibited. Unit shall be Eemax or approved equal.

RATINGS OF "THERMOSTATIC" MODELS { cold or hot water feed }

	THERMOSTATIC OPTION	VOLTS	kW	AMPS	TEMPERATURE RISE °F					MINIMUM RECOMMENDED
MODEL					0.5 GPM	0.75 GPM	1.0GPM	1.5 GPM	2.0 GPM	WIRE SIZE
EX2412T	S,P,FS,DR	120V	2.4kW	20A	33°	22°	16°	11°	8°	10AWG
EX3012T	S,P,FS,DR	120V	3.0kW	25A	41°	27°	20°	14°	10°	10AWG
EX3512T	S,P,FS,DR	120V	3.5kW	29A	48°	32°	24°	16°	12°	10AWG
EX48T	EE,ML,S,P,FS,DR	240V*	4.8kW	20A	65°	44°	32°	21°	16°	12AWG
EX55T	EE,ML,S,P,FS,DR	240V*	5.5kW	23A	75°	50°	38°	25°	19°	10AWG
EX65T	EE,ML,S,P,FS,DR	240V*	6.5kW	27A	89°	59°	44°	30°	22°	10AWG
EX75T	EE,ML,S,P,FS,DR	240V*	7.5kW	32A	_	68°	51°	34°	26°	8AWG
EX95T	EE,ML,S,P,FS,DR	240V*	9.5kW	40A	_	87°	65°	43°	32°	8AWG
EX8208T	EE,ML,S,P,FS,DR	208V	8.3kW	40A	_	76°	57°	38°	28°	8AWG
EX60T	EE,ML,S,P,FS,DR	277V	6.0kW	22A	81°	55°	41°	27°	20°	10AWG
EX80T	EE,ML,S,P,FS,DR	277V	8.0kW	29A	_	73°	55°	36°	27°	10AWG
EX90T	EE,ML,S,P,FS,DR	277V	9.0kW	33A	_	82°	61°	41°	31°	8AWG
EX100T	EE,ML,S,P,FS,DR	277V	10.0kW	36A	_	91°	68°	46°	34°	8AWG

^{*} Units can be used at 208V with 25% reduced output and amperage.

THERMOSTATIC TEMPERATURE CONTROL SPECIFICATION OPTIONS

☐ EE = (Emergency Eye Wash) to specify tepid water thermostatic units. Example: EX95TEE

Flows greater than 3 GPM consult "Series Two" (T2 Models) or "Three Phase" (T3 Models) specification sheet

ML = (Multiple Lavs) .5 GPM x one, two or three handwash lavs, factory set temp 105° with .5 GPM turn on (5.5kW - 10kW)

Example: EX95TML {includes one, two, or three .5 GPM aerators (EX61) note quantities}

= (Sanitation Setting) thermostat set to 180°. Example: EX95TS

= (Photo Setting) temperatures lower than 100°F. Example: EX95TP

☐ FS = (Factory Set) temperature ambient to 180° Example: <u>EX95FS 105°</u>

☐ DR = External temperature control, LED temperature display (see "Digital Readout" spec)

SPECIFICATIONS:

Dimensions: 10.75"x5.25"x2.78"

Weight: 3 lbs.

Cover: ABS UL rated 94Vo.

Color: White

Standard temperature range 100°F-140°F

Element: Replaceable Ni Chrome cartridge insert


Fittings: 1/2" pipe compression fittings at bottom of unit. (5%" OD)

UL Listed: E86887 (M)

U.S. Patent #'s: 4,762,980 and 4,960,976

SPECIAL DESIGN **SERVICE** INQUIRIES FOR UNITS FOR UNIQUE APPLICATIONS ARE WELCOME. CALL OUR TECHNICAL SERVICE DEPT.

1-800-543-6163





EEMAX SUBMITTAL								
Engineer/Architect: Job Name/Customer: _								
_ocation:								
Contractor:								
Representative:								
HEATER SPECIFICATI								
			Option	Quantity	kW	Voltage	AMPS	GPM
Thermostatic Model #	EX	Т						

353 Christian St., Oxford, CT 06478

www.eemax.com

Telephone: (203) 267-7890 Toll Free: 1-800-543-6163 Fax: (203) 267-7975