



Description/Application

The T-K3-Pro is a fully modulating, gas fired, tankless on-demand water heaters specifically designed for light commercial applications. It can be either installed outdoors, indoors or direct vented. It can supply to domestic hot water systems or to heating applications (local codes dictate proper compliance). Features HRS35 copper alloy and a thicker heat exchanger drum for added durability. Up to 4 units can be easily linked without a multi-unit controller in systems for larger applications. Please check local codes prior to installations.

Fuel: NG or LP

Safety Features

- Built in Freeze Protection
- Manual Reset Hi Limit (Set at 194°F)
- Overheat Cut Off Fuse
- Inlet, Outlet & Mixing Thermistors for Constant Temperature Monitoring
- Air Fuel Ratio Rod
- GFI Power Supply Connection
- Flame Sensor

Venting and Combustion

- 4" Category III Stainless Steel
- Vertical or Horizontal Installation
- 50' Max Length, 5 elbows max (90° elbows = 5' equivalent length)
- Power Vent
- Electronic Ignition
- 3" Combustion Air Intake (with optional kit)
- 55 dB Noise Level at Max Output

Accessories

- TK-TV10 Direct Vent Conversion Kit (optional)
TM-RE30 Temperature Remote Control (optional)
- 400' Max Distance From Water Heater
- Non-Polarized 18 Gauge Control Wiring
- TM-TV13 Wall Ventilation Termination (direct vent)
TK-RB01 Recess Box (optional)
TK-PC01 Pipe Cover (optional)
TK-TV04 Vent Cap (optional)
TK-BF01 Backflow Preventor (optional)
TK-KPWL4 & TK-KPWH4 T-Vent Terminations (optional)


Temperature Settings

Dip Switch: 104°F 113°F 122°F (default) 131°F 140°F 158°F 176°F 185°F


TM-RE30 Remote Controller

Default Mode: 99°F 100°F 102°F 104°F 106°F 108°F 110°F 111°F 113°F 115°F 117°F
122°F (default) 131°F 140°F 158°F 167°F

High Temp Mode: 99°F 100°F 102°F 104°F 106°F 108°F 110°F 111°F 113°F
122°F (default) 131°F 140°F 149°F 158°F 167°F H (176°F or 185°F depends on dipswitch setting)



Above shown rate is based on single unit only




Takagi Industrial Co. USA, Inc.

5 Whatney Irvine, CA 92618
888.882.5244 www.takagi.com

Met SCAQMD rule 1146.2 (certified by BR Lab)



Model T-K3-Pro



T-K3-Pro:

	HT	W	D	WT	Volt	Amp	Flue	Intake	(Hot/Cold/Gas) Connections
	20.5"	13.8"	8.5"	40 lbs.	120	0.77	4" O.D.*	3.0" O.D. (opt.)	3/4" NPT
	Input		Input		Energy Factor		Thermal Eff.	AFUE	Min Press
	Max BTU/h		Min BTU/h						Max. Press
NG	199,000		11,000		0.827		82.3%	0.80	5.0" W.C.
LP	199,000		11,000		0.833		83.6%	0.81	8.0" W.C.
	GPM		Water PSI		Coil Cap				
	0.5 - 7.0**		15 - 150 PSI***		≈0.2 Gallons				
Clearances		Top	Bottom	Front	Back	Sides			
Indoor		12"	12"	4"	1"	2"			
Outdoor		36"	12"	24"	1"	2"			

* Category III Required **Current numbers based on factory testing, 0.4 GPM Required for Continuous Fire After initial Ignition.

***Pressure Only Relief Valve Requires (Min. 200,000 BTUs. 150 PSI). Min 40 PSI or above recommended for maximum flow.

Warranty: **10 years Heat Exchanger, 5 years Parts (for Residential Use) - 3 years Heat Exchanger, 3 years Parts (for Commercial Use)**

Specification

Water heater(s) shall be Model T-K3-Pro as manufactured by Takagi Industrial Company, Inc. The water heater(s) shall be a copper coil integral fin and tube construction with quick release brass or bronze waterways. Heater(s) will be factory assembled and tested.

The heater shall be vented with 4" Stainless steel Category III vent pipe a distance not to exceed 50' (equivalent) feet terminating vertically or horizontally as prescribed. Intake air with optional direct vent kit may be of such material as PVC not to exceed a total of 50' (equivalent).

The heater(s) shall be controlled by onboard solid state printed circuit board monitoring incoming and outgoing temperatures with factory installed thermistors, sensing and controlling flow rate to set point temperature with control both air and gas mixture inputs to maintain thermal combustion efficiency. Unit also consists of ground fault interrupter, inline fusing, spark ignition and sensor system, aluminized stainless steel burners, air-fuel ratio rod, Hi limit switch, modulating and proportional gas valves, freeze protection sensor and heating block and overhead cut-off fuses.

The water heater(s) shall be CSA listed, exceeds the energy efficiency requirements of ASHRAE 90. 1b-1992 and listed by SCAQMD rule 1146.2 Low NOx.