Robertshaw.



Seven Day Comfort Control Simplified

The Robertshaw® RS6000 thermostat family is Simply the Right Choice™ when it comes to daily programmable temperature controls that can save energy and money.

With the comfort, convenience, and efficiency features that homeowners and contractors want, the RS6000 family provides EnergyStar® and California Title 24 compliant features for an affordable price.

- Fully programmable with soft touch keys to easily set four events per day AND 7 day scheduling.
- Copy command that makes programming simple to set up and flexible to use.
- Pop-Up Wizard to customize thermostat settings with an instant start-up menu.

The RS6000 thermostats are fully compatible with all standard 24V AC heating and cooling systems. Additional compatibility with multi-stage gas/electric furnaces and heat pump systems are available in the RS6220 and RS6320 models.

Add in easy installation, Contractor ID option, and quality you can depend on, and you have the Robertshaw RS6000 thermostat family - Simply the Right Choice.

RS6110 RS6220 RS6320

VALUE SERIES
DIGITAL PROGRAMMABLE
THERMOSTATS











ELECTRIC

GAS

OIL

HEAT PUMP MILLIVOLT

7 Day Programmable

RS6110 - 1 Heat / 1 Cool

RS6220 – Universal Control up to 2 Heat / 2 Cool RS6320 – Universal Control up to 3 Heat / 2 Cool

Features and Benefits

Universal Control up to 2 Heat / 2 Cool – RS6220 only Universal Control up to 3 Heat / 2 Cool – RS6320 only Operates on both multi-stage gas/electric furnaces and heat pumps means less inventory.

Auto Changeover

Switches automatically between heating and cooling for constant home comfort.

Pop-Up Wizard

Launches instant installation menu to quickly enter the settings for programmed thermostat functions.

Bigger Brighter Backlight with Nightlight Option

Makes viewing and setting the temperature easier any time of the day.

Worry-Free Memory Retention

Maintains set point and programmed parameters, even during power outages.

Easy Change Battery Access

Provides drop down removable compartment for quick battery replacement.

Circulating Fan

Maintains optimal air circulation between demand cycles for improved comfort with minimal energy use.

Low Temperature Freeze Protection

Turns on heat automatically when temperature goes below 41°F. Protects pipes from freezing.

Adjustable Temperature Differential and Upstaging

Provides for full selection of parameters to deliver maximum comfort or energy savings.

High and Low Setpoint Limits


Protects the heating and cooling systems by limiting temperature settings.

An ISO 9001 - 2000 Certified Company












RS6110 RS6220 RS6320

VALUE SERIES DIGITAL PROGRAMMABLE THERMOSTATS

Terminal Designations



Heat Active 24V AC Reversing

Cooling Relay (Stage 1)

RS6220 and RS6320 (RC) C (Y1) (W1)(Y2)(RH/R) (G) (B 0 24V AC Cool Active

Fan Relay (Cooling) 24V AC Heat Activ 24V AC ransforme Reversing Valve (Heating)

Relay (Stage 1)

Cooling Relay (Stage 2)

Heating

(W2)

Heating

Relay (Stage 2)

Emergency or 3rd Stage Heating Relay

(E)

L

System

Technical Specifications

24V AC

Product Weight	12.8 oz.
Electrical Rating	24V AC (18-30V AC)
	1 amp maximum load per terminal
	3 amp total maximum load
	(all terminals combined)
Temp. Control Range	45°F to 90°F (7°C to 32°C)
Accuracy	± 1°F (± 0.5°C)
Power	24V AC with battery back-up OR 3.0V DC
	(2 AA alkaline batteries included)
System Configurations	Two stage gas, electric, oil, millivolt, and
	up to three stage heat pump systems
Terminations	RS6110 – RH/R, RC, C, G, B, O, Y1, W1
	RS6220 / RS6320 – RH/R, RC, C, G, B, 0,
	Y1, W1, Y2, W2, E, L

Shipping Specifications

Individual Carton Dimensions 6.75" x 4.375" x 1.625"

Master Carton Quantity 6

Master Carton Dimensions 9.25" x 5.625" x 7.625"

Master Carton Weight 5 lbs. Pallet Quantity 1170

40" x 48" x 48" Pallet Dimensions

Replacement Chart

Reversing Valve

RS6110		
Braeburn®	5000, 5050	
Honeywell	TH6110D	
White-Rodgers	1F80-0471	
RS6220		
Braeburn®	5300	
Lux	PSPA722E	
Honeywell	TH6220D	
White-Rodgers	1F85-0471	
RS6320		
Honeywell	TH6320D	
White-Rodgers	1F85-0471	

Verify specific application requirements before substitution.

invensys. Controls

©2008 Invensys Controls

191 E. North Avenue Carol Stream Illinois 60188 USA Customer Service Telephone 1.800.304.6563 Customer Service Facsimile 1.951.737.8261 iccacustomerservice@invensys.com www.RobertshawTstats.com www.invensyscontrols.com