

Non-Programmable, Heat Only

SimpleComfort® 1600/1601 Thermostats

Simple control for year-round comfort. This easy-to-operate comfort command center allows you to match temperature to your family's lifestyle. Attractive, extra-rugged, highly reliable and accurate, this thermostat's elegant design will look and perform like new for years to come.



- Simple operation
- Large LCD display
- Low battery indicator (SC1600)
- No batteries required (SC1601)
- Compatible with gas, oil and hydronic systems
- Freeze protection feature

SC1600




SC1601



**Non-Programmable
Heat Only
Thermostat**

- Single-stage heat
- For gas, oil and hydronic systems
- Millivolt compatible (SC1600)
- No fan output

Dimensions



Specifications

Electrical Rating:

- 24 VAC (18-30 VAC)
- 1 amp maximum per terminal
- 1 amp maximum total load
- 60-minute power backup (SC1601)
- Easy access terminal block

Temperature Control Ranges:

- 45°F to 90°F, Accuracy: $\pm 1^\circ\text{F}$

System Configurations:

- Single-stage heat, gas, oil and hydronic

Terminations:

- SC1600: R, W
- SC1601: R, C, W



*Look for the full line of quality
ICM SimpleComfort® thermostats
at your HVAC distributor.*

Specifications subject to change without notice.



SC3006 Thermostat shown with
ACC-WP02 insulated wall plate.



ACC-WP02

ACC-WP01

**Need more wall
coverage?
Choose an ICM insulated
wall plate for a polished
installation.**

Eliminate the wall effect. ICM insulated wall plates provide a fast, easy solution for hiding wall problems.

- Foam gasket prevents drafts through wall opening
- Rugged, flexible construction
- Hidden mounting screws (included) for a sleek appearance
- Wall plates designed to work with ICM's 1000, 2000 and 3000 series thermostats

Choose from two convenient sizes:

- **ACC-WP01** — 4 $\frac{27}{32}$ " x 5 $\frac{15}{16}$ "
- **ACC-WP02** — 5 $\frac{19}{32}$ " x 7 $\frac{1}{2}$ "