



**DOUBLE WALL  
INDIRECT WATER HEATER**

**Submittal Sheet**

**EGD-Sub-01**

**DOUBLE WALL ENERGY SAVER INDIRECT WATER HEATERS**

**JOB NAME** \_\_\_\_\_

**LOCATION** \_\_\_\_\_

**ARCH./ENGR.** \_\_\_\_\_

**WHOLESALE** \_\_\_\_\_

**MECH. CONTRACTOR** \_\_\_\_\_

**MODEL NO.** \_\_\_\_\_

**TYPE GAS** \_\_\_\_\_

**Btu/hr INPUT** \_\_\_\_\_

**RECOVERY RATE IN GPH** \_\_\_\_\_ **@** \_\_\_\_\_ **°F RISE**

**GALLON CAPACITY** \_\_\_\_\_


**NOTES**

---

**Standard Features**

- Non-CFC Foam Insulation
- Glass-Lined Steel Tank
- Large Capacity Double Wall, Glass Coated Heat Exchanger Coil
- (2) Aluminum Tank Saver Anode Rods
- Dielectric Nipples
- Adjustable Thermostat
- Temperature and Pressure Relief Valve
- Brass Drain Valve
- Warranty - *Ten year limited tank warranty.  
Six year warranty on parts.  
(See warranty for details)*

# Double Wall Energy Saver Indirect Dimensions and Specifications



**NOTE:** The uniform plumbing code limits the boiler pressure relief valve to 30 psi when installing in a potable water system.

Model	Gal. Cap.	1st Hour Rating @140°F	1st Hour Rating @115°F	A	B	D	E	F	Shipping Weight
EGD040	38	139	208	41-1/4"	22"	27-1/2"	5-1/2"	34-1/2"	170
EGD050	48	146	216	46-1/4"	22"	27-1/2"	5-1/2"	40-1/4"	180
EGD065	64	154	223	59"	22"	27-1/2"	5-1/2"	53-1/4"	196
EGD080	75	165	234	59"	24"	27-1/2"	5-1/2"	53"	224

**Notes:** All water connections are 3/4" NPT on 8" centers.  
 All heat exchanger connections are 3/4" NPT.  
 All ratings are based on 180°F boiler water temperature, 50°F potable water inlet temperature and an approximate boiler output of 220,000 Btu/Hr.

## Certified for Potable Water and Space Heating Applications

This water heater is suitable for water heating and space heating. Toxic chemicals, such as those used for boiler water treatment shall NEVER be introduced into the potable water system. This water heater may NEVER be connected to any existing heating system or components previously used with non-potable water heating appliances.

All models available with a Ten Year Limited Warranty Against Tank Failure. All parts are warranted for six years. Three year limited warranty on all models when installed in a commercial application.



Lochinvar Corporation • 300 Maddox Simpson Pkwy • Lebanon, TN 37090 • 615-889-8900/Fax: 615-547-1000

www.Lochinvar.com