

Job Name : _____
 Purchaser : _____
 Engineer : _____
 Submitted To : _____
 Submitted By : _____
 Unit Designation : Schedule No.: _____

Location : _____
 P.O. No. : _____
 Architect : _____
 Date : _____
 For : Reference Approval Construction
 Model No.: _____




Submittal Data : Through-The-Wall Air Conditioners


Standard Features :

- Five Year Parts and Labor Warranty on Sealed Refrigerant System
- One Year Full System Warranty on Parts and Labor, 2-5 Year Parts
- R-22 Refrigerant
- High Energy Efficiency
- Digital Control Display
- Wireless Remote Controller
- Temperature Display on unit
- Auto Restart
- Energy Saver Mode
- Gold Fin™ Anti-corrosion Treatment for Condenser
- 3 Fan Speed (H/M/L for Cool/Fan for Cooling Only)
2 Fan Speed (H/L for Cool/Heat/Fan for Heat Cool)
- Unit Dimension (inches, WxHxD) :
24 x 14 13/32 x 20 3/32 (Cooling Only)
24 21/32 x 14 13/32 x 19 21/32 (Heat Cool)
- Wall Sleeve Dimension (inches, WxHxD, optional) :
25 7/8 x 15 17/32 x 16 23/32
25 5/16 x 14 7/8 x 15 5/16 (inside)
Depth with Front Grille
20 1/2" (Cooling Only), 20" (Heat Cool)


Unit (Cooling Only)



Unit (Heat Cool)



Trim (with the Unit)



Unit Specification :

(Cooling Only)

Model No.	Cooling Capacity (Btu/h)	EER	Electric Heating Capacity (Btu/h)	Power Supply (V,Ph,HZ)	Air Circulation (CFM, H/L)	Dehumidification (pts/hr)	Running Current (A)		Power Input (Watts)		Maximum Overcurrent Protection (A)	Weight Net/Gross (lbs)
							Cooling	Electric Heating	Cooling	Electric Heating		
LT0810CR	8,000	9.6	-	115,1,60	260/220	2.2	7.5	-	830	-	15	73/80
LT1010CR	9,800	8.8	-	115,1,60	285/225	3.2	10.2	-	1,110	-	15	78/85
LT1030CR	10,000/9,800	9.4/9.4	-	230/208,1,60	285/225	3.2	4.7/5.2	-	1,060/1,040	-	15	78/85
LT1210CR	11,500	8.8	-	115,1,60	290/230	3.8	12.0	-	1,300	-	15	80/87
LT1230CR	11,500/11,200	8.8/8.8	-	230/208,1,60	290/230	3.8	6.0/6.4	-	1,310/1,270	-	15	80/87
LT1430CR	13,000/12,600	8.5/8.5	-	230/208,1,60	310/250	4.0	7.0/7.5	-	1,530/1,480	-	15	87/94


(Heat Cool)

Model No.	Cooling Capacity (Btu/h)	EER	Electric Heating Capacity (Btu/h)	Power Supply (V,Ph,HZ)	Air Circulation (CFM, H/L)	Dehumidification (pts/hr)	Running Current (A)		Power Input (Watts)		Maximum Overcurrent Protection (A)	Weight Net/Gross (lbs)
							Cooling	Electric Heating	Cooling	Electric Heating		
LT1030HR	10,000/9,800	9.4/9.4	11,200/9,200	230/208,1,60	285/225	3.2	4.7/5.2	15.3/14.0	1,060/1,040	3,500/2,900	20	80/87
LT1230HR	11,500/11,200	8.8/8.8	11,200/9,200	230/208,1,60	290/230	3.8	6.0/6.4	15.3/14.0	1,310/1,270	3,500/2,900	20	81/88


Accessories :

Wall Sleeve (26"Wx15 17/32"Hx16 23/32"D)	AXSVA1A-1
Architecture Grille - Aluminum	AXAGALA01A
Stamped Aluminum Grille	AXRGALA01

Wall Sleeve



Architecture Grille



Stamped Aluminum Grille



Note :