

## DRAIN PAN SEALANT



### Pan-Coat®

Pan-Coat® is an epoxy drain pan repair that permanently seals drain pan leaks while preventing further rust and corrosion. The Pan-Coat® formula is based around a ceramic filled novolac 2 part epoxy system that has high cross linked density, but contains no solvents or VOC's. This robust coating can withstand substances ranging from Sulfuric acid (75%), to diesel fuel, to ethylene glycol, all the way down to brine water. Once cured (4-6 hours) Pan-Coat® has a smooth, light gray composition.

Some of Pan-Coat's® advantages are minimal surface preparation, the ability to bond to wet or damp substrates, as well as being able to cure under water. Pan-Coat's® self-leveling formula allows for even coverage and creates a strong, permanent impact resistant bond with the surface, be it wood, metal, or concrete. Other Pan-Coat® uses include sump and cooling tower repair.

**Pot Life:** 40° F: 9 hours  
75° F: 1hour  
95° F: 40 Minutes

**Cure Time:** 75 °F: 4-6 hours

**Flash Point:** 250° F

**Coverage:** Gallon: 160 square feet @10 mils  
Quart: 40 square feet @10 mils  
Bag: 8 square feet @10 mils

**Recommended Thickness:** 2 coats of 8-12 mils each

**Volatile Organic Compounds (VOC's):** 0 grams/liter

**Pull-off Adhesion Test ASTM D-4541:** Mid adhesion 2750 psi

CATALOG NO.	DESCRIPTION	ORDER UOM	ORDER MULT.	LIST PRICE
PC-1B	Pan-Coat® Bag of Sealant	EA	27	\$65.72
PC-1Q	Pan-Coat® 1 Quart Sealant	EA	9	\$117.24
PC-1G	Pan-Coat® 1 Gallon Sealant	EA	4	\$379.68