



SimpleComfort® SC2201N

Terminations

R C Y1 W2 O B G E

HEAT PUMP ONLY: 2-STAGE HEAT/1-STAGE COOL

Non-Programmable

Simple control for year-round comfort. This easy-to-operate comfort command center allows you to match temperature to your family's lifestyle. Attractive, extra-rugged, highly reliable and accurate, this thermostat's elegant design will look and perform like new for years to come.



- For heat pumps only
- Two-stage heat/one-stage cool
- Single-compressor heat pump system with auxiliary heat
- New ICM patented Thermal Intrusion Barrier
- Simple operation
- Large LCD display (backlight model available; see ordering information)
- Accuracy: $\pm 1^{\circ}\text{F}$
- Manual changeover
- Adjustable temperature differential
- Hardwired
- 30-minute power loss memory retention
- Emergency heat mode
- Zone compatible
- Soft touch controls
- Status LEDs






SC2201N



- For heat pumps only
- Two-stage heat/single-stage cool
- Zone compatible
- Manual changeover

Non-Programmable
For heat pumps only
Two-Stage Heat/Single-Stage Cool
Hardwired

Dimensions



Specifications

Electrical Rating:

- 24 VAC (18-30 VAC)
- 1 amp maximum per terminal
- 3 amp maximum total load
- 30-minute power loss memory retention
- Easy access terminal block

Temperature Control Ranges:

- 45°F to 90°F, Accuracy: $\pm 1^\circ\text{F}$

System Configurations:

- For heat pumps only
- Two-stage heat/single-stage cool
- Single-compressor heat pump system with auxiliary heat

Terminations:

- R, C, Y1, W2, O, B, G, E

Ordering Information*:


- Without backlight: SC2201N
- With backlight: SC2201L

* Pricing varies per model

Specifications subject to change without notice.

NEW Thermal Intrusion Barrier

Exclusive, patented insulation technology eliminates thermal drift caused by wall effect.



If you like this model, be sure to try out these other thermostats from ICM Controls!

SimpleComfort® PRO Series – Innovation and technology that simplifies installation and increases profitability!

- Flexible 7-day, 5-2-day and 5-1-1-day programming (programmable models)
- ICM's patented Thermal Intrusion Barrier
- ICM's patent-pending SimpleSet™ Target Programming technology
- Large display with backlight
- Permanent memory
- Auto or manual changeover
- Field adjustable calibration
- Configurable remote sensor compatible
- Keypad lockout
- Soft-touch controls

Programmable Thermostats

SC5010 – One-stage heat/cool or heat pump, dual powered

SC5011 – One-stage heat/cool or heat pump, hardwired

SC5211 – Two stage heat pump, hardwired

SC5811 – Two-stage heat/cool or heat pump, hardwired

SC5812 – Three-stage heat/two-stage cool or heat pump, dual fuel compatible, hardwired

Non-Programmable Thermostats

SC4010 – One-stage heat/cool or heat pump, dual powered

SC4011 – One-stage heat/cool or heat pump, hardwired

SC4211 – Two stage heat pump, hardwired

SC4811 – Two-stage heat/cool or heat pump, hardwired

SC4812 – Three-stage heat/two-stage cool or heat pump, dual fuel compatible, hardwired