



# Frost Sentry™

S1 S2 W G R

## FS 1500L/FS 1500VL GARAGE THERMOSTAT

**HEAT ONLY**

*Non-Programmable*

**This easy-to-operate garage thermostat** allows you to maintain temperature to your garage/storage area. Attractive, extra-rugged, highly reliable and accurate, this thermostat will look and perform like new for years to come. Ideal for garages, warehouse, storage facilities, etc..



- Controls Single Stage Heating Systems
- Millivolt and Hydronic (water or steam) System Compatible
- Compatible with Gas and Electric Systems
- Battery Operated
- Backlit Display
- Mercury-Free, Environmentally Safe
- Remote sensor compatible (ACC-RT104)
- **FS1500L** – Horizontal
- **FS1500VL** – Vertical





# FS1500L/FS1500VL

- One-stage heat
- Gas, oil or electric systems
- FS1500L – Horizontal
- FS1500VL – Vertical

## Non-Programmable Single-Stage Heat

### Specifications

#### Electrical Rating:

- 24 VAC (18-30 VAC)
- 1 amp maximum per terminal
- 2 amp maximum total load
- Easy access terminal block

#### Temperature Control Ranges:

- 35°F to 75°F, Accuracy:  $\pm 1^\circ\text{F}$

#### System Configurations:

- Single-stage heat, gas, oil, electric




#### Terminations: S1, S2, W, G, R

#### Ordering Information:



- FS1500L – Horizontal
- FS1500VL – Vertical

### Dimensions

FS1500L – Horizontal design




FS1500VL – Vertical design



## NEW Thermal Intrusion Barrier

Exclusive, patented insulation technology eliminates thermal drift caused by wall effect.



If you like this model, be sure to try out these other thermostats from ICM Controls!

SimpleComfort® PRO Series – Innovation and technology that simplifies installation and increases profitability!

- Flexible 7-day, 5-2-day and 5-1-1-day programming (programmable models)
- ICM's patented Thermal Intrusion Barrier
- ICM's patent-pending SimpleSet™ Target Programming technology
- Large display with backlight
- Permanent memory
- Auto or manual changeover
- Field adjustable calibration
- Configurable remote sensor compatible
- Keypad lockout
- Soft-touch controls

### Programmable Thermostats

- SC5010 – One-stage heat/cool or heat pump, dual powered
- SC5011 – One-stage heat/cool or heat pump, hardwired
- SC5211 – Two stage heat pump, hardwired
- SC5811 – Two-stage heat/cool or heat pump, hardwired
- SC5812 – Three-stage heat/two-stage cool or heat pump, dual fuel compatible, hardwired

### Non-Programmable Thermostats

- SC4010 – One-stage heat/cool or heat pump, dual powered
- SC4011 – One-stage heat/cool or heat pump, hardwired
- SC4211 – Two stage heat pump, hardwired
- SC4811 – Two-stage heat/cool or heat pump, hardwired
- SC4812 – Three-stage heat/two-stage cool or single or dual heat pump, hardwired

Specifications subject to change without notice.

Patent No. Design: 424,953  
 Patent No. Thermal Intrusion Barrier: 6,597,275  
 Patent Pending SimpleSet™ Target Programming

1-800-365-5525  
[www.icmcontrols.com](http://www.icmcontrols.com)

