

## EP Branch Multi-port Tee

Submittal Information

Revision A: Feb. 27, 2009

### Project Information

Job Name:

Location:

Part No. Ordered:

Engineer:

Date Submitted:

Contractor:

Submitted By:

Manufacturer's Representative:

Approved By:

### Technical Data

Material:	UDEL GF120
Maximum Temperature (no pressure):	320°F (160°C)
Maximum Working Temperature /Pressure:	210°F (99°C) at 150 psi



### Product Information and Application Use

EP Branch Multi-port Tee features an integrated ¾" or 1" ProPEX® inlet with ½" ProPEX branch outlets.<sup>1</sup> The tee is designed for commercial plumbing applications, and eliminates the need for multiple connections. The elbow is made of EP, which is proven in demanding hot-water applications.

✓ Description	Part Number	Length	Height	Width	Weight
¾" EP Branch Multi-port Tee, 7 outlets	Q2277550	8.66"	2.10"	1.77"	0.327 lbs.
¾" EP Branch Multi-port Tee, 8 outlets	Q2287550	9.50"	2.10"	1.77"	0.362 lbs.
1" EP Branch Multi-port Tee, 10 outlets	Q2101051	11.60"	2.10"	1.77"	0.437 lbs.
1" EP Branch Multi-port Tee, 12 outlets	Q2121051	13.40"	2.10"	1.77"	0.505 lbs.

### Installation

Any product designed to mount 1¼" copper pipe (for the EP Branch Multi-port Tee) may be used as a mounting bracket. For more information, refer to the AquaPEX® Professional Plumbing Installation Handbook.

### Standards

CAN/CSA B137.5; ASTM F877; ASTM F1960

### Codes

IPC; UPC; NSPC; NPC of Canada

### Listings

ANSI/NSF 14- and 61-certified; ICC ESR 1099; IAPMO 3946

### Related Applications

PEX-a Plumbing Systems

### Contact Information

Uponor, Inc.  
5925 148<sup>th</sup> Street West  
Apple Valley, MN 55124 USA  
Phone: (800) 321-4739  
Fax: (952) 891-2008  
www.uponor-usa.com

Uponor Ltd.  
2000 Argentia Rd., Plaza 1, Ste. 200  
Mississauga, ON L5N 1W1 CANADA  
Phone: (888) 994-7726  
Fax: (800) 638-9517  
www.uponor.ca

<sup>1</sup>ProPEX® is a registered trademark of Uponor, Inc. ProPEX™ is a trademark of Uponor Ltd.