





Location :			
P.O. No. :			
Architect :			
Date :			
For :	Reference	Approval	Construction
Model No.:			




Heat Pump Single Zone Mini Split

LSN122HE

Heating Nominal Test Condition :
Indoor : 70 DB / 60 WB
Outdoor : 47 DB / 43 WB
Pipe Length : 25ft



LSU122HE



Maximum Length (ft)	50
Maximum Height Difference (ft)	25
Liquid Side (inches, O.D)	1/4
Gas Side (inches, O.D)	1/2
Refrigerant	R410A

Cooling Operating Range (, standard)	0 - 115
Heating Operating Range ()	14 - 75

- Five Year Compressor Warranty
- Two Year Functional Parts Warranty
- Plasma Air Purifying System
- Chaos Swing Air Circulation
- Jet Cool™
- LCD Wireless Remote Controller
- Auto Restart
- 24 Hour On/Off Timer
- Built-in Low Ambient Standard down to 0 °C at cooling mode

Technical drawing of the LG 2000 Series refrigerator, showing front and side views with dimensions.

Front View Dimensions:

- Top width: 30 5/16
- Top width (inner): 10 27/32
- Left height: 45 1/2
- Right height: 21 5/16
- Bottom height (from floor): 33 3/2
- Bottom height (from floor, including feet): 3 15/16

Side View Dimensions:

- Top width: 9 5/8