For Non-Health Hazard Applications

Job Name	Contractor
Job Location	Approval
	Contractor's P.O. No.
	Representative

Series N9

Dual Check Vacuum Breakers for In-Line Applications

Size 1/4" and 3/8" (8 and 10mm)

Series N9 Dual Check Vacuum Breakers for In-Line Applications are used for continuous pressure, non-health hazard, applications. These valves have NPT female inlet and outlet connection and brass body construction.

Models


N9C - same as N9 except comes with chrome body

Pressure-Temperature

Temperature Range: 33°F – 140°F (5°C – 60°C) Maximum Working Pressure: 125psi (8.6 bars)

Applications

Series N9 should be installed on each parlor sink where a hose is attached. This series is for use on continuous pressure applications.



Dimensions — Weights

MODEL	SIZE	(DN)	DIMENSIONS							WEIGHT	
			Α		В		B1				
	in.	mm	in.	mm	in.	mm	in.	mm	lbs.	kgs.	
N9C	1/4	6	23/8	60	11/4	32	1	25	.38	.17	
N9C	3/8	10	23/8	60	11/4	32	1	25	.38	.17	
N9	1/4	6	23/8	60	11/4	32	1	25	.38	.17	
N9	3/8	10	23/8	60	11/4	32	1	25	.38	.17	



N9

Capacity kPa psi 345 50 310 45 276 40 241 35 207 30 138 20 103 15 69 10 35 5 0 0 0

3


15

Flow

19

2

7.6



USA: 815 Chestnut St., No. Andover, MA 01845-6098; www.wattsreg.com **Canada:** 5435 North Service Rd., Burlington, ONT L7L 5H7; www.wattscda.com





6

23

7 gpm

27 lpm

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.

0

0

3.8