

EP Flow-through Opposing-port Multi-port Tee

Submittal Information Revision A: March 6, 2008

Project Information

Job Name:

JOB Harrie.		
Location:	Part No. Ordered:	
Engineer:	Date Submitted:	
Contractor:	Submitted By:	
Manufacturer's Representative:	Approved By:	

Technical Data

Material: UDEL GF120
Maximum Temperature (no pressure): 320°F (160°C)

Maximum Working Temperature/Pressure: 210°F (99°C) at

150 psi



Product Information and Application Use

EP Flow-through Opposing-port Multi-port Tee features ¾" ProPEX inlets with opposing ½" ProPEX branch outlets. These are designed for central location to facilitate piping in two directions. The tee is made of EP, which is proven in demanding hot-water applications.

✓ Description	Part Number	Length	Height	Width	Weight
EP Flow-through Opposing-port Multi-port Tee, 3 outlets, ¾" x ¾" ProPEX EP Flow-through Opposing-port Multi-port Tee, 4 outlets, ¾" x ¾" ProPEX EP Flow-through Opposing-port Multi-port Tee, 6 outlets, ¾" x ¾" ProPEX	Q2337557	4.41"	2.38"	1.18"	0.072 lbs.
	Q2347557	4.41"	2.38"	1.18"	0.077 lbs.
	Q2367557	5.66"	2.38"	1.18"	0.108 lbs.

Installation

Any product designed to mount ¾" PEX tubing (for the EP Flow-through Opposing-port Multi-port Tee) may be used as a mounting bracket. For more information, refer to the AQUAPEX® Professional Plumbing Installation Handbook.

Standards

CAN/CSA B137.5; ASTM F877; ASTM F1960

Codes

IPC; UPC; NSPC; NPC of Canada

Listings

ANSI/NSF 14- and 61-certified; ICC ESR 1099; IAPMO 3946

Related Applications	Contact Information					
PEX-a Plumbing Systems	Uponor, Inc. 5925 148 th Street West Apple Valley, MN 55124 USA Phone: (800) 321-4739 Fax: (952) 891-2008 www.uponor-usa.com	Uponor Ltd. 655 Park Street Regina, SK S4N 5N1 CANADA Phone: (888) 994-7726 Fax: (800) 638-9517 www.uponor.ca				

¹ProPEX[®] is a registered trademark of Uponor, Inc. ProPEX [™] is a trademark of Uponor Ltd.