

# Poly Tape

Made in  
America



## DESCRIPTION

Poly Tape is a convenient and easy-to-use product which complements the Nomaco Insulation tubing and sheet insulation products. It is supplied in 3 mil thickness by 2" width by

36 yards, with a solvent acrylic adhesive for applying to hot or cold pipes and fittings. The factory-applied acrylic adhesive adheres well on polyolefin foam tube and sheet insulation and forms a long-lasting bond. Poly Tape is designed to perform in direct sunlight and is 25/50 rated for flame spread and smoke developed.

## USES

Poly Tape is waterproof, weatherproof and designed for indoor or outdoor use.

Its function is to cover circumferential/butt joints, copper couplings and press fittings to ensure the seams from popping open.

## APPLICATION INSTRUCTIONS

When using Poly Tape, first clean insulation surface where tape is to be applied. Surface must be cleaned free of dirt, scale, moisture, oil and grease. Tape length should be 1-1/2 (one and one half) times the length of the joint. This will allow for tape overlap and maximum adhesion.

Position and adhere tape securely at circumferential/butt joint or solderless fitting. Apply firm, even pressure around entire circumference of the joint or fitting to assure the tape adhesive is properly engaged. To prevent compression of the insulation at the joint, care should be exercised so that tape is not applied too tightly.

## Physical Properties

Skin Surface	Smooth, black surface for excellent appearance
Composition	UV resistant polypropylene film with solvent acrylic "CW" adhesive
Color	Black
Dimensions	3 mils x 2" (48 mm) x 36 yards (32.9 m) roll • 12 rolls per master carton
Tensile	22 lb/inch (2.5 cm)
Elongation	150%
Mold Growth	0
Temperature Limits	-35°F (-37°C) to 260°F (127°C)
Freight Classification	Tape, insulation, NOIBN. No label required