

Company name: Created by: Phone: Fax: -

| Position Co | Count | Description | | Unit price |
|---------------|-------|--------------|--|------------|
| | 1 | UPS 26-99 FC | | On |
| | | | | request |

Date:



Product photo could vary from the actual product

Product No.: 52722512

The pump is of the canned rotor type, i.e. pump and motor form an integral unit without shaft seal and with only two gaskets for sealing.

The bearings are lubricated by the pumped liquid.

The pump is characterized by:

- * Ceramic shaft and radial bearings.
- * Carbon axial bearing.
- * Stainless steel rotor can and bearing plate.
- * Corrosion-resistant impeller, Composite, PES.
- * Cast ironpump housing.

The motor is a 1-phase motor.

No additional motor protection is required.

Liquid:

Liquid temperature range: 35.6 .. 230 °F

Technical:

Maximum operating pressure: 145 psi Approvals on nameplate: UL, CSA

Materials:

Pump housing: Cast iron

EN-JL1030 ASTM 30 B

Impeller: Composite, PES

Installation:

Maximum ambient temperature: 104 °F
Ambient max at 176°F liquid: 176 °F
Maximum operating pressure: 145 psi
Flange standard: USA Oval
Type of connection: C.I. Flange
Pipe connection: 2 - Bolt Flange

Pressure stage: 10
Port-to-port length: 6 1/2 in

Electrical data:




Company name: Created by: Phone: Fax: Date: -



Company name: Created by: Phone: Fax: -

Date:

52722512 UPS 26-99 FC 60 Hz







Company name: -

Created by: - Phone: -

Fax: Date:

52722512 UPS 26-99 FC 60 Hz





Note! All units are in [mm] unless others are stated. Disclaimer: This simplified dimensional drawing does not show all details.