

THIS SPACE FOR DESIGNER/ENGINEER APPROVAL

Job/Customer _____	Date _____	Contractor _____
Model Specified _____	Qty _____	Approved By _____
Designer/Engineer _____	Date _____	Contractor's PO# _____
Submitted by _____	Date _____	Other _____

4143 Series

Full Port Forged Brass Ball Valves

w/ Hi-Flow Hose Drain

& Reversible Handle



IPS Union x IPS

600 WOG

ISO 9001



ITEM #	SIZE	CTN	CASE	A	B	C	D	E	F
41433	3/4"	6	24	3/4	4 5/8	2 1/16	4	2 7/16	1/2
41434*	1"	4	16	1	4 11/16	2 5/8	4 1/16	2 1/2	1/2
41435	1 1/4"	2	12	1 1/4	4 11/16	3	4 5/16	2 5/16	3/4
41436*	1 1/2"	2	12	1 1/2	5 5/8	3 1/2	5 3/16	3 1/8	3/4



NO.	DESCRIPTION	MATERIAL
1	BODY	BRASS
2	END CAP	BRASS
3	SEAT	PTFE
4	BALL	BRASS HCP
5	STEM	BRASS
6	STEM SEAL	PTFE
7	PACKING GLAND	BRASS
8	LEVER HANDLE	STAINLESS STEEL
9	HANDLE JACKET	VINYL
10	HANDLE NUT	STAINLESS STEEL
11	UNION NUT	BRASS
12	FITTING	BRASS
13	O-RING	EPDM
14	END CAP	BRASS
15	SEAT	PTFE
16	BALL	BRASS HCP
17	STEM	BRASS
18	STEM SEAL	PTFE
19	PACKING GLAND	BRASS
20	HANDLE	ENAMEL COATED ALUMINUM
21	HANDLE SCREW	BRASS
22	CAP & STRAP	BRASS
23	WASHER	EPDM

TEMP °F	WOG
100	600
150	490
200	470
250	439
300	411
350	294
366	N/A

Specifications: Designed for residential, commercial or industrial use with water, oil or gas. This approved Webstone valve is actuated by a blowout proof stem and features an adjustable packing gland. Threaded ends comply with ANSI B1.20.1. ***Style is not yet available; refer to page 2 for current specifications.**

Webstone Company, Inc.
www.webstonevalves.com

Quality and Commitment Since 1954

Tel: (800) 225-9529 • Fax (800) 336-5133

Webstone product specifications in U.S. customary units are approximate and are provided for reference only. Webstone reserves the right to change or modify product design, construction, specifications or materials without prior notice and without incurring any obligation to make such changes and modifications on Webstone products previously or subsequently sold.

4143spec_110310

THIS SPACE FOR DESIGNER/ENGINEER APPROVAL

Job/Customer _____	Date _____	Contractor _____
Model Specified _____	Qty _____	Approved By _____
Designer/Engineer _____	Date _____	Contractor's PO# _____
Submitted by _____	Date _____	Other _____

4143 Series

**Full Port Forged Brass Ball Valves
w/ Hi-Flow Hose Drain, Single Union End
& Reversible Handle**



IPS Union x Hose x IPS

600 WOG

ISO 9001



ITEM #	SIZE	CTN	CASE	A	B	C	D	E	F
41433	3/4"	4	32	3/4	4 3/8	2	3 5/8	2 7/16	1/2
41434	1"	2	24	1	5 1/8	2 3/8	4 11/16	2 1/2	1/2
41435	1 1/4"	2	16	1 1/4	6 1/4	2 5/8	4 11/16	2 3/4	3/4
41436	1 1/2"	1	16	1 1/2	6 7/8	3 7/16	5 3/16	3	3/4



NO.	DESCRIPTION	MATERIAL
1	BODY	BRASS
2	END CAP	BRASS
3	SEAT	PTFE
4	BALL	BRASS HCP
5	STEM	BRASS
6	STEM SEAL	PTFE
7	PACKING GLAND	BRASS
8	LEVER HANDLE	STEEL CP
9	HANDLE JACKET	VINYL
10	HANDLE NUT	STEEL ZP
11	UNION NUT	BRASS
12	FITTING	BRASS
13	WASHER	EPDM
14	UNION RING	ABS
15	END CAP	BRASS
16	SEAT	PTFE
17	BALL	BRASS HCP
18	STEM	BRASS
19	STEM SEAL	PTFE
20	PACKING GLAND	BRASS
21	HANDLE	ENAMEL COATED ALUMINUM
22	HANDLE SCREW	BRASS
23	CAP & STRAP	BRASS
24	WASHER	EPDM

TEMP °F	WOG
100	600
150	490
200	470
250	439
300	411
350	294
366	N/A

Specifications: Designed for residential, commercial or industrial use with water, oil or gas. This approved Webstone valve is actuated by a blowout proof stem and features an adjustable packing gland. Threaded ends comply with ANSI B1.20.1.

Webstone Company, Inc.
www.webstonevalves.com

Quality and Commitment Since 1954

Tel: (800) 225-9529 • Fax (800) 336-5133

Webstone product specifications in U.S. customary units are approximate and are provided for reference only. Webstone reserves the right to change or modify product design, construction, specifications or materials without prior notice and without incurring any obligation to make such changes and modifications on Webstone products previously or subsequently sold.

4143spec_110310