


GRUNDFOS INSTRUCTIONS Installation and Operation

Maintenance-free Timer and Thermostatic Control Accessories

Old Style Terminal Box
UP Models with Date
Codes between
9132 and 0527



1. Application

Grundfos timer and thermostatic control accessories are designed only for use with specified Grundfos Series UP circulators installed in indoor hot water service systems. Applicable Series UP models include all single speed, 1-phase, 115 volt, 60 hertz pumps with date codes between 9132 and 0527. (NOTE: These accessories are not intended for use with the Model UPS15-42F, UPS15-58FC 3-speed circulators.)

The timer control is designed to turn the circulator on and off at preset times, allowing the user to select operation of the circulator during high use periods of the day.

The thermostatic control automatically turns the circulator off when the temperature in the hot water line exceeds approximately 130°F (as the case of periods with no demand) and back on when the temperature falls below approximately 110°F (as in the case of periods with high demand).

When the timer and thermostatic controls are installed together, in series, the circulator operates ONLY at the preset clock times specified by the user AND ONLY when the temperature conditions of the thermostat are met. That is, if either the timer control or the thermostatic control switch is open (off), the circulator will not operate.

2. Technical Data

TIMER CONTROL

Supply Voltage: 115-120 VAC, 60 hertz

Contact Rating: 16 amps

Ambient Temperature: -4°F to 175°F

Shortest Switching Interval: 15 minute increment

Switch Modes: "Timer", "ON" Override, "OFF" Override

Protection: Clear plastic cover for dust and moisture protection of the clock face

THERMOSTATIC CONTROL

Supply Voltage: 115-120 VAC, 60 hertz

Contact Rating (resistive): 5.8 amps

Type: Surface sensing, snap acting bimetallic disc

Enclosure: Environmentally sealed

Switch Modes:

Low Temp Model

105 ± 5°F (40 ± 2°C) pump switches OFF

85 ± 6°F (29 ± 3°C) pump switches ON

High Temp Model


115 ± 5°F (46 ± 2°C) pump switches OFF

105 ± 5°F (40 ± 2°C) pump switches ON

3. Installing the Timer Control

POSITION OF PUMP MOTOR SHAFT AND TERMINAL BOX

All Series UP circulators MUST be installed with the motor shaft in the horizontal position. The pump terminal box MUST be located on top or to either side of the motor housing.



3. Installing the Timer Control

Contact Position: Normally closed
Mounting: (1/2") Clip-on type for 5/8" O.D. system piping size (i.e., 1/2" I.D. copper tubing or 3/8" steel pipe)
(3/4") Clip-on type for 7/8" O.D. system piping size (i.e., 3/4" I.D. copper tubing or 1/2" steel pipe)
May be mounted on either the inlet or outlet piping of the circulator.

LIMITED WARRANTY

Products manufactured by GRUNDFOS PUMPS CORPORATION (GRUNDFOS) are warranted to the original user only to be free of defects in material and workmanship for a period of 24 months from date of installation, but not more than 30 months from date of manufacture. GRUNDFOS' liability under this warranty shall be limited to repairing or replacing at GRUNDFOS' option, without charge, F.O.B. GRUNDFOS' factory or authorized service station, any product of GRUNDFOS manufacture. GRUNDFOS will not be liable for any costs of removal, installation, transportation, or any other charges which may arise in connection with a warranty claim. Products which are sold but not manufactured by GRUNDFOS are subject to the warranty provided by the manufacturer of said products and not by GRUNDFOS' warranty. GRUNDFOS will not be liable for damage or wear to products caused by abnormal operating conditions, accident, abuse, misuse, unauthorized alteration or repair, or if the product was not installed in accordance with GRUNDFOS' printed installation and operation instructions.

To obtain service under this warranty, the defective product must be returned to the distributor or dealer of GRUNDFOS products from which it was purchased together with proof of purchase and installation date, failure date, and supporting installation data. Unless otherwise provided, the distributor or dealer will contact the GRUNDFOS factory or authorized service station for instructions. Any defective product to be returned to the factory or service station must be sent freight prepaid; documentation supporting the warranty claim and/or a Return Authorization must be included if so instructed.

GRUNDFOS WILL NOT BE LIABLE FOR ANY INCIDENTAL OR CONSEQUENTIAL DAMAGES, LOSSES, OR EXPENSES ARISING FROM INSTALLATION, USE, OR ANY OTHER CAUSES. THERE ARE NO EXPRESS OR IMPLIED WARRANTIES, INCLUDING MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE, WHICH EXTEND BEYOND THOSE WARRANTIES DESCRIBED OR REFERRED TO ABOVE.

Some jurisdictions do not allow the exclusion or limitation of incidental or consequential damages and some jurisdictions do not allow limitations on how long implied warranties may last. Therefore, the above limitations or exclusions may not apply to you. This warranty gives you specific legal rights and you may also have other rights which vary from jurisdiction to jurisdiction.

Grundfos Pumps Corp.
17100 W.118th Terrace
Olathe, Kansas 66061
Telephone: (913) 227-3400
Fax: (913) 227-3500

Grundfos Canada, Inc.
2941 Brighton Rd.
Oakville, Ontario L6H 6C9
Telephone: (905) 829-9533
Fax: (905) 829-9512


Bombas Grundfos de Mexico, S.A. de C.V.
Boulevard TLC #15,
Parque Industrial Stiva Aeropuerto
C.P. 66600 Apodaca, N.L. Mexico
Telephone: 52-81-8144-4000
Fax: 52-81-8144-4010

L-UP-TL-091 Rev.10/05
PRINTED IN USA

INSTALLATION PROCEDURE

The timer control accessory is electrically connected and mounted to the circulator terminal box. Install as follows:

1. Remove the retaining screw in the existing terminal box cover and remove the cover. The timer control unit replaces this cover.
2. See "5. Electrical Hookup", for specific wiring instructions for hookup as an individual component or in series with the thermostatic control.
3. After wiring is completed and checked, install the timer control unit onto the terminal box bracket and reinsert the terminal box screw. Be careful not to bind or leave exposed any terminal box wires.



4. Installing the Thermostatic Control

INSTALLATION PROCEDURE


1. The thermostatic control is a surface temperature sensing device that must be in contact with the system piping to operate properly. Separate models include clip-on mounts for 3/4" (7/8" O.D.) and 1/2" (5/8" O.D.) copper tubing. These models are also suitable for use with 12" and 3/8" schedule 40 steel pipe, respectively.
2. See "5 Electrical Hook-up", for specific wiring instructions for hook-up as an individual component or in series with the timer control.



5. Electrical Hook-up


All electrical work should be performed by a qualified electrician in accordance with the latest edition of the National Electric Code and local codes and regulations.

Verify the electrical supply to be certain the voltage, phase and frequency match that of the circulator and accessory components.




WIRING DIAGRAM FOR TIMER AND THERMOSTAT
(Wired in Series)


6. Setting and Operating the Timer Control and Starting the Pump



CAUTION: Do not energize pump until properly installed




WIRING DIAGRAM FOR TIMER CONTROL ONLY



WIRING DIAGRAM FOR THERMOSTATIC CONTROL ONLY

NOTE: Before the circulator is started, the system must be filled with liquid and vented.

1. Set the timer switch to the actual time by turning the programming ring in the direction of the arrow until the timing arrow points to the actual time on the ring.
2. Switch on the power supply to the circulator and set the manual switch to the "ON" position. The circulator will now start.
3. Set the required "ON"/"OFF" times on the programming ring by pushing the programming tabs either away from or toward the center of the ring. Tabs pushed away from the center indicate circulator switched "ON" while tabs pushed toward the center indicate circulator switched "OFF".



4. Set the manual switch to the "TIMER" position. The circulator will now start/stop according to the settings of the programming tabs.
5. For continuous operation, set the manual switch to the "ON" position. To switch the circulator off, set the manual switch to the "OFF" position. The "ON"/"OFF" modes may be used without affecting the function of either the programming ring or the timer switch.
6. In case of power outage the timer will not keep time. After power has been restored, the correct time of day must be reset by rotating the programming ring in the direction of the arrow until the timing arrow points to the actual time on the ring.