

Submittal Data: System 18CL ASU18CL & AOU18CL



Job Name:	Location:			
Purchaser:				
Engineer:				
Submitted To:	For:	<input type="checkbox"/> Reference	<input type="checkbox"/> Approval	<input type="checkbox"/> Construction
Submitted By:				

OUTLINE AND DIMENSIONS

Capacities:

Cooling	18,000 BTU/h
Min/Max Cooling	5,500/19,000BTU/h
Outdoor Design Temperature <i>F° DB/WB</i>	95/75
SEER	19.0
EER	10.4
Low Ambient Temp. <i>F°</i>	14
Voltage/Frequency/Phase	208-230/60/1

Indoor Unit:

Noise Level <i>db (A) - H/ M/ L/ Q</i>	44/38/32/25
Weight	20 lbs.


Outdoor Unit:

Noise Level <i>db (A)</i>	50
Recommended Fuse Size	20A
Min. Ampacity	16A
Running Current <i>(Rated/Max)</i>	7.7/9.0
Weight	88 lbs.

Refrigerant Piping:

Max Ht. Difference	49 ft.
Max Total or Combined Length	66 ft.
Discharge Vapor Line (O.D.)	1/4 in.
Suction (O.D.)	1/2 in.

Note: Figures are based on 230 Volts



Standard Features:

- ♦ Six year compressor warranty
- ♦ Two year parts warranty
- ♦ Refrigerant R410A
- ♦ Auto Mode; Quiet Mode
- ♦ Auto Louver: Up/Down
- ♦ Apple Catechin Filter
- ♦ Auto Changeover
- ♦ Digital Wireless Remote Control
- ♦ Sleep timer; 24 hour timer
- ♦ Built in Low Ambient
- ♦ Auto Restart/ Reset
- ♦ Dry Mode; Coil Dry Mode
- ♦ Cold Prevention
- ♦ Ion Deodorizing Filter
- ♦ Optional Wired Remote Control

Notes: