

Submittal Data: System 24RCLX AUU24RCLX & AOU24RLX



Job Name: _____ Location: _____

Purchaser: _____

Engineer: _____

Submitted To: _____ For: Reference Approval Construction

Submitted By: _____

Capacities:

Cooling	22,200 BTU/h
Min/Max Cooling	5,000-27,300BTU/h
Outdoor Design Temperature <i>F° DB/WB</i>	95/75
Heating	24,200 BTU/h
Min/Max Heating	5,000-29,000BTU/h
Outdoor Design Temperature <i>F° DB/WB</i>	47/43
HSPF	8.5
SEER	15.0
EER <i>Cooling/Heating</i>	10.6/10.2
Low Ambient Temp. <i>F° Cooling/Heating</i>	0/14
Voltage/Frequency/Phase	208-230/60/1

Indoor Unit:

Noise Level Cooling <i>db (A) - H/ M/ L</i>	45/43/38
Noise Level Heating <i>db (A) - H/ M/ L</i>	43/39/35
Weight	75 lbs.
Total Height	9-3/4 in.
Space required above ceiling	8-1/2 in.

Outdoor Unit:


Noise Level <i>db (A) - Cooling/Heating</i>	53/55
Recommended Fuse Size	20A
Min. Ampacity	15.4A
Running Current Cooling <i>(Rated/Max)</i>	9.2/12.5
Running Current Heating <i>(Rated/Max)</i>	10.4/12.5
Weight	141 lbs.

Refrigerant Piping:

Max Ht. Difference	65 ft.
Max Total or Combined Length	165 ft.
Discharge Vapor Line (O.D.)	3/8 in.
Suction (O.D.)	5/8 in.

Note: Figures are based on 230 Volts

OUTLINE AND DIMENSIONS



Standard Features:

- ◆ Six year compressor warranty
- ◆ Two year parts warranty
- ◆ Weekly timer
- ◆ Auto Louver: Up/Down
- ◆ Energy saver; Slender Fit
- ◆ Pump Down Operation
- ◆ Full Function Wired Remote Control
- ◆ Cold Prevention
- ◆ Built in Low Ambient
- ◆ Auto Restart/ Reset
- ◆ Refrigerant R410A
- ◆ High Ceiling Mode
- ◆ Branch Duct Capable
- ◆ Auto Mode; Quiet Mode; Dry Mode

Notes:
