



Product information presented here reflects conditions at time of publication. Consult factory regarding discrepancies or inconsistencies.

MAIL TO: P.O. BOX 16347 • Louisville, KY 40256-0347  
SHIP TO: 3649 Cane Run Road • Louisville, KY 40211-1961  
(502) 778-2731 • 1 (800) 928-PUMP • FAX (502) 774-3624

visit our web site:  
[www.zoeller.com](http://www.zoeller.com)

## A-PAK ALARM SYSTEMS

### INDOOR/OUTDOOR ALARM SYSTEM FEATURES

- Indoor & Outdoor use per UL 864
- Alarm system (horn & light) operates to warn of a high water condition
- Horn is rated 82 decibels at 10'
- Alarm Test and Horn Silence Switch with auto reset
- Terminal connections for a pump & float switch

#### Standard Model (P/N 10-0623) Includes:

- 15 ft. float switch

#### Deluxe Model (P/N 10-0682) Includes:

- 20 ft. float switch
- 6 ft. power cord plugs into 115V outlet
- Watertight cord connectors

### “A-PAK” ALARM SYSTEM FEATURES (115V/1Ph/9V DC)

- Auto reset solid state alarm
- 9 Volt battery back-up (battery not included)
- NEMA 1 non-corrosive enclosure for indoor use
- Manual shut off
- Float operates on 12 VAC
- Float switch with 15' cable included
- 6 ft. power cord plugs into 115V outlet
- Horn is rated at 86 decibels at 10'

\* Auxiliary dry contacts

### “A-PAK II” ALARM SYSTEM FEATURES 10-0126 (115V/1Ph)

- NEMA 4X thermoplastic alarm panel
- Horn & light warn of high liquid levels
- Test and silence switch
- Auxiliary dry high level alarm contacts - 5 amps
- Operates on separate circuit from pump 115 VAC
- UL Listed for US & Canada
- Float switch with 15 ft. cable included
- Can be used with liquids to 140°F (60°C)
- Horn is rated at 88 decibels at 10'

### 10-0015 (115V) / 10-0016 (230V)


- Non-enclosed model
- 6" magnetic bell with transformer
- Mount on standard utility box (not included)
- Operates with 10-0743 float switch or mechanical alternator (not included)



# A-PAK ALARM SYSTEMS

## 10-0028 (115V/1Ph)

- Non-Enclosed model.
- Operates on 115V circuit.
- 3" magnetic bell with transformer.
- Mount on standard utility box. (Not Included).
- Float switch with 15 ft. cable included.



Note: All variable level float switches in this section are mechanically activated and do not contain mercury.

# A-PAK PUMP ALARM SYSTEMS

MODEL #	VOLTS	PANEL	SWITCH	AUX. CONTACTS	UL	CSA
10-0015	115V	N/A	Alarm Float P/N 10-0743 <sup>(1)</sup>	N/A	No	No
10-0016	230V	N/A	Alarm Float P/N 10-0743 <sup>(1)</sup>	N/A	No	No
10-0028	115V	N/A	Alarm Float 15' Cable	N/A	No	No
10-0126	115V	6" x 4" x 4" NEMA 4X	Alarm Float 15' Cable	115V	Yes	Yes <sup>(2)</sup>
10-0623	115V	6.5" x 4.5" x 3.0" NEMA 3R	Alarm Float 15' Cable	N/A	Yes	Yes
10-0682	115V	6.5" x 4.5" x 3.0" PVC/UL Indoor/Outdoor Watertight Cord Connectors	Alarm Float 20' Cable	N/A	Yes	Yes
10-1494	115V and 9V Battery	NEMA 1 for indoor use.	Mechanical Float 15' Cable	N/A	Yes	Yes
10-2613	115V and 9V Battery	NEMA 1 for indoor use.	Vertical Reed Float 15' Cable	N/A	Yes	Yes
10-2614	115V and 9V Battery	NEMA 1 for indoor use.	Mechanical Float 15' Cable	Yes	Yes	Yes
10-2615	115V and 9V Battery	NEMA 1 for indoor use.	Vertical Reed Float 15' Cable	Yes	Yes	Yes

<sup>(1)</sup> Alarm Float Switch not included. Purchase separately. See FM0526 or use float switch listed (Includes 15' cable).

<sup>(2)</sup> List to Canadian Standard cULus.