

JOB:		REPRESENTATIVE:	
UNIT TAG:		ORDER NO.	DATE:
ENGINEER:		SUBMITTED BY:	DATE:
CONTRACTOR:		APPROVED BY:	DATE:



Lead Free^{*}, Energy Efficient e³ ecocirc Circulators for Potable Water Application



Description

e³ circulators are energy efficient circulators using permanent magnet, ECM (electronically commutated motor) technology. The e³ circulators are designed specifically for potable water applications. These circulators are lead free^{*} and come with a variety of options including a temperature sensor, various body styles, assembled with electrical cord and plug, timer and more.

Materials of Construction

Pump Body: Lead Free^{*} Brass
O-Ring: EPDM or Viton
Bearing: Carbon/Alumina Ceramic
Impeller: Nylon/PPO
Motor: High Efficiency ECM
All Other Wetted Parts: Type 316 Stainless Steel
Shaft-less, seal-less construction

Operating Data

Pump

Maximum Working Pressure: 150 psi (10.3 Bar)
Maximum Working Temperature: 230°F (110°C)
Minimum Working temperature: 50°F (10°C)

Motor

ECM Spherical Motor
100-240V 50/60HZ
5-28 Watts Power Consumption
Automatic Overload Protection
Low in-rush current

Adjustable Speed Switch (Models Without Temp Sensor)

Infinitely variable-speed switch to manually adjust motor speed.

Adjustable Temperature Sensor (Fixed Speed Only)

Adjustable Set Point from 68 to 158 °F (20° to 70°C)
Turns circulator OFF when water temperature reaches set point
Turns circulator ON when water temperature is 10°F (6°C) below set point

Connections

1/2" UltraCirc
1/2" Sweat
1/2" FNPT Threaded

^{*} As defined by CA AB1953. Applies to sweat and threaded housing.

Standard Features

Motor

Designed with a shaftless spherical motor with permanent magnet technology for improved efficiency.

Lead Free

All e³ circulators are made from lead free^{*} construction

Optional Features

Adjustable Speed Switch

This switch is only available on models without the internal temperature sensor. A stepless motor switch allows infinite motor speed variation.

Adjustable Temperature Sensor

This built-in temperature sensor is adjustable and will turn the circulators off when it reaches the set point and turn the circulators back on when the temperature is more than 10°F (6°C) below the set point. Only available on fixed-speed motors.

Body Types

UltraCirc: The UltraCirc comes with 1/2" union connections and has a built in air purger to remove unwanted air. The UltraCirc also has a built in check and isolation valves for easy isolation and removal of motor housing.

Sweat: The e³ circulators have the option of a 1/2" sweat connection.

Threaded: The e³ circulators have the option of 1/2" female NPT.

Plug

e³ circulators have the option to be pre-wired with a 6 ft. electrical plug. For fastest installation, install the circulators into the piping and simply plug the circulator into a standard outlet.

Timer


e³ circulators can provide an even greater increase in energy savings when used in combination with the e³-Timer. The timer is easily installed by removing the motor end cap, plugging in the timer and setting the timer schedule.

Special Specifications


The contractor shall furnish and install in-line circulating pumps as illustrated on the plans and in accordance with the following specification:

1. The pumps shall be of the high efficiency type specifically designed for quiet operation
2. Pump to be suitable for 230°F (110°C) operation at 150 psig (10.3 Bar) working pressure
3. The pumps shall have a ceramic ball bearing lubricated by the system fluid.
4. Pump body shall be lead-free (less than 0.25% Pb) brass*
5. Pump to have (1) of following options:
 - a) Pump to have built-in adjustable thermostat from 68°F to 158°F (20°C to 70°C)
 - b) Pump to have built-in stepless speed switch
6. Motor shall be spherical permanent magnet electrically commutated motor (ECM)
7. Motor shall be non-overloading at any point on the pump curve and shall have built in overload protection
8. Pumps to have a capacity of ____ GPM at ____ foot of head
9. All pumps to be supplied by Bell & Gossett Model _____

e³-4 Pump Curves



e³-6 Pump Curves



Part Number	Model	Material	Connection		Adjustable Speed	Adjustable Thermostat	Plug
			Size	Type			
LHB08100101	e ³ -4V/BSPYZ	LEAD-FREE BRASS*	1/2"	SWEAT	.		.
LHB08100102	e ³ -4V/BSXRZ	LEAD-FREE BRASS*	1/2"	SWEAT		.	
LHB08100104	e ³ -4V/BTXYZ	LEAD-FREE BRASS*	1/2"	FNPT	.		
LHB08100106	e ³ -4V/BTPRZ	LEAD-FREE BRASS*	1/2"	FNPT		.	.
LHB08100107	e ³ -4V/BUPYZ	BRASS	1/2"	UNION	.		.
LHB08100108	e ³ -4V/BUPRZ	BRASS	1/2"	UNION		.	.
LHB08100109	e ³ -6V/BSPYZ	LEAD-FREE BRASS*	1/2"	SWEAT	.		.
LHB08100112	e ³ -6V/BTXYZ	LEAD-FREE BRASS*	1/2"	FNPT	.		
LHB08100110	e ³ -6V/BTPYZ	LEAD-FREE BRASS*	1/2"	FNPT	.		.
LHB08100111	e ³ -6V/BUPYZ	BRASS	1/2"	UNION	.		.
LHB08260002	e ³ -TIMER						

*As defined by CA AB1953. Applies to sweat and threaded housing.