

ProPEX® Ball Valve

Submittal Information
Revision B: Oct. 21, 2009

Project Information

Job Name:

Location:

Part No. Ordered:

Engineer:

Date Submitted:

Contractor:

Submitted By:

Manufacturer's Representative:


Approved By:

Technical Data

Material: CA 360 Brass
Maximum Working Temperature: 250°F (121°C)
Maximum Working Pressure: 250 psi (17 bar)

Product Information and Application Use

The Uponor ProPEX® Ball Valve products include 3/4" copper adapters and feature in-line isolation valves.¹



✓ Description	Part Number	A	B	C	D	Weight
ProPEX Ball Valve, 5/8" PEX x 3/4" Copper Adapter	Q5806375	3.19"	1.81"	5/8"	3/4" Copper	0.50 lbs.
ProPEX Ball Valve, 3/4" PEX x 3/4" Copper Adapter	Q5807575	3.43"	1.67"	3/4"	3/4" Copper	0.50 lbs.

Installation

Install valve according to local building code. Do not dismantle. If soldering, aim flame away from fitting. For more information, refer to the AquaPEX® Professional Plumbing Installation Guide or Radiant Floor Installation Handbook.

Standards

CSA 137.5; B125; ASTM F877; ASTM F1960

Codes

IPC; UPC; NPC of Canada

Listings

IAPMO 3960; NSF 61- and 9-certified

Related Applications

PEX-a Plumbing Systems
Radiant Heating and Cooling Systems
Snow and Ice Melting Systems
Permafrost Protection Systems
Turf Conditioning Systems

Contact Information

Uponor, Inc.
5925 148th Street West
Apple Valley, MN 55124 USA
Phone: (800) 321-4739
Fax: (952) 891-2008
www.uponor-usa.com

Uponor Ltd.
2000 Argentia Rd., Plaza 1, Ste. 200
Mississauga, ON L5N 1W1 CANADA
Phone: (888) 994-7726
Fax: (800) 638-9517
www.uponor.ca

¹ProPEX® is a registered trademark of Uponor, Inc. ProPEX™ is a trademark of Uponor Ltd.