

FQ SERIES QUIET FAN LIGHTS

Models: FQ80FL, FQ110FL

Fantech ENERGY STAR® qualified Quiet Exhaust Fan Lights are designed with energy efficient motors and fluorescent lights. Permanently lubricated PSC motor is rated for continuous operation to meet the recommendations of ASHRAE 62.2. White grille features frosted lens. One 26W compact fluorescent light and 4 watt night light are included. Fan, light and night light can be wired separately.

FEATURES

MOTOR:

- Permanently lubricated PSC ball bearing motor rated for continuous use
- Thermal overload protection
- 120 volts; 60 hz

HOUSING:

- Rugged galvanized metal housing with rust-proof paint
- 4" duct diameter
- Integrated backdraft damper
- 5 adjustable hanger bars for easy installation between 16" to 24" on-center studs

GRILLE:

- White polymeric grille with frosted lens
- Attaches to housing with torsion springs
- Energy efficient 26W CFL light included
- 4W night light included

OTHER:

- Product is UL Listed for use over tub/shower enclosures when installed with GFCI branch circuit wiring.
- UL Listed for use in insulated ceilings (TYPE IC)
- The Home Ventilating Institute (HVI) has tested and certified airflow performance (CFM) and sound levels (sones) of these products.
- Fans are ENERGY STAR® qualified
- California Title 24 compliant
- Fans meet the standard of the Washington State Ventilation and Indoor Air Quality Code.

WARRANTY

- 5 Year Warranty

TYPICAL SPECIFICATIONS


Fan shall be Fantech Model FQ80FL (FQ110FL) ENERGY STAR® qualified ceiling mount type fan light with night light. Unit shall be rated for continuous operation.

Air performance shall be certified by the Home Ventilating Institute (HVI) to be no less than 80 (110) CFM @ 0.1" sp with sound levels no greater than 0.4 (1.3) sones.

Fan Light shall be constructed with a galvanized steel housing, built-in backdraft damper, adjustable hanger bars and 4" duct diameter discharge.

Unit shall feature an ENERGY STAR® qualified light fixture with 26W compact fluorescent lamp (included) and 4 watt night light (included).

Fan Light shall be UL and cUL Listed for tub/shower when used with GFCI branch circuit wiring. Fan Light shall be UL Listed for use in insulated ceilings (TYPE IC).





SHIPPING INFORMATION – SINGLE CARTON

- Box: 16 3/4" x 14" x 12"
- Shipping Wt.: 12 lbs.

Specification			Project:
Reference	Quantity	Comments	Location:
			Architect:
			Engineer:
			Contractor:
			Submitted by:
			Date:


PERFORMANCE RATINGS

FQ80FL/FQ110FL AIR FLOW PERFORMANCE



FAN SPECIFICATIONS

Model	Power Consumption (W)				Airflow (CFM) @ 0.1 sp	Sones
	Power	Motor	Light (CFL)	Night Light		
FQ80FL	120V/60 Hz	25	26W	4W	80	0.4
FQ110FL	120V/60 Hz	30	26W	4W	110	1.3



Fantech

United States

10048 Industrial Blvd.
 Lenexa, KS 66215
 Phone: 800.747.1762; 913.752.6000
 Fax: 800.487.9915; 913.752.6466
www.fantech.net; info@fantech.net

Canada

50 Kanalfakt Way,
 Bouctouche, NB E4S 3M5
 Phone: 800.565.3548; 506.743.9500
 Fax: 877.747.8116; 506.743.9600

Fantech reserves the right to modify, at any time and without notice, any or all of its products' features, designs, components and specifications to maintain their technological leadership position.

Item #: 400074
 Rev Date: 72611