

ProPEX® Lead-free (LF) Brass Elbow, ½" PEX x ½" MIP

Submittal Information

Revision B: Jan. 27, 2010

Project Information

Job Name:

Location:

Part No. Ordered:

Engineer:

Date Submitted:

Contractor:

Submitted By:

Manufacturer's Representative:

Approved By:

Technical Data

Material:	C69300 Brass
Maximum Temperature (no pressure):	320°F (160°C)
Maximum Working Temperature/Pressure:	210°F at 150 psi (99°C at 10 bar)



Product Information and Application Use

Uponor's ProPEX® Lead-free Brass Elbow with Membrane Interface Probe (MIP) makes 90-degree connections for ½" Uponor AquaPEX® tubing to ½" Male NPT thread.¹

✓ Description	Part Number	Length	Width	Height	Weight
ProPEX LF Brass Elbow, ½" PEX x ½" MIP	LF4125050	1.75"	1.50"	1.75"	0.12 lbs.

Installation

ProPEX Tool and ProPEX Rings (sold separately) are required for connecting the PEX tubing. Use the appropriate ProPEX Ring for connecting to PEX tubing. Refer to the AquaPEX Professional Plumbing Installation Guide or Radiant Floor Heating Installation Handbook for additional information.

Standards

CAN/CSA B137.5; ASTM F877; ASTM F1960

Codes

IPC; UPC; NSPC; NPC of Canada

Listings

IAPMO 3558; ANSI/NSF 14- and 61-certified; HUD MR 1269; ICC ESR 1099; U.P. Code, Annex G

Related Applications

PEX-a Plumbing Systems
Radiant Heating and Cooling Systems
Snow and Ice Melting Systems
Permafrost Protection Systems
Turf Conditioning Systems

Contact Information

Uponor, Inc.
5925 148th Street West
Apple Valley, MN 55124 USA
Phone: (800) 321-4739
Fax: (952) 891-2008
www.uponor-usa.com

Uponor Ltd.
2000 Argentia Rd., Plaza 1, Ste. 200
Mississauga, ON L5N 1W1 CANADA
Phone: (888) 994-7726
Fax: (800) 638-9517
www.uponor.ca

¹ProPEX® is a registered trademark of Uponor, Inc. ProPEX™ is a trademark of Uponor, Ltd.