



High-quality, architecturally pleasing,  
innovative access doors for walls, ceilings,  
ducts, floors and roofs



# FLUSH for Drywall DW-5040

## Application

- Designed specifically for installation in drywall walls and ceilings after the drywall has been installed

## Product Features

- Formed door panel with flanges on four sides
- Unique concealed hinge, door flange is a perforated tapping bead with pre-punched holes

## DW-5040 Access Door Specifications:

**Material:** 20 gauge galvanized formed door panel, flanged on four sides;  
26 gauge galvanized frame, with multiple bends for added strength.

**Door:** Formed door panel, flanged on four sides, Integral perforated tapping bead adds extra rigidity

**Hinge:** Concealed

**Standard Latch:** Screwdriver operated cam latch

**Optional Latches/Locks:** Cylinder lock & key; allen head cam latch; spanner head cam latch

**Finish:** 5 stage iron phosphate preparation with white baked polyester powder coat on door panel. Frame to be mill finish



## AVAILABLE SIZES (Special sizes available upon request)

NOMINAL DOOR SIZE W X H		WEIGHT PER DOOR		
inches	mm	Latches	lbs.	kg.
6 X 6	152 X 152	1	1.5	.68
8 X 8	203 X 203	1	2.0	.91
10 X 10	254 X 254	1	2.5	1.14
12 X 12	305 X 305	1	3.0	1.36
14 X 14	355 X 355	1	5.0	2.27
16 X 16	406 X 406	1	5.5	2.5
18 X 18	457 X 457	1	6.0	2.73
22 X 22	560 X 560	2	8.0	3.64
24 X 24	610 X 610	2	9.0	4.09
24 X 36	610 X 914	2	13.0	5.91
30 X 30	762 X 762	2	15.0	6.82
36 X 36	914 X 914	2	21.0	9.55

Wall or ceiling opening is  $W + 3/8"$  ( 9 mm)  
For detailed specifications see submittal sheet

