

PEERLESS®

PARTNER®

INDIRECT-FIRED WATER HEATER

5 Sizes ■ 30 to 119 Gallon Capacity ■ 234 to 564 GPH First Hour Rating

Features:

Uses the Existing Boiler as its Heat Source

- No Separate Chimney or Burner Required
- Functions as an Additional Heating Zone

Long Lasting Stainless Steel Construction

- High Grade 316L Stainless Steel Tank
- Superior Corrosion Resistance
- Drain Tapping for Draining and Flushing Tank

Cupronickel Fin-Tube Heat Exchanger

- Provides Maximum Heat Transfer for Rapid Recovery Rates
- Resists Mineral Buildup and Scaling Deposits
- 1" Boiler Connections Provide for Minimum Pressure Drop thru Heat Exchanger

Minimal Standby Temperature Loss

- 2" Polyurethane Foam Insulation
- Less Than 1/2° F per Hour Standby Loss
- Minimal Boiler Firing to Maintain Temperature
- Provides More Hot Water with Reduced Boiler Water Temperatures

Maintenance-Free Plastic Jacket

- Will Not Scratch or Rust
- Color Coordinated to Match Peerless Boiler Jackets

Enclosed Thermostat Well

- Control Can Be changed Without Draining Tank



Standard Equipment:

- Honeywell Well Type Adjustable Control
- T & P Relief Valve
- Cupronickel Fin-Tube Heat Exchanger
- High Grade 316L Stainless Steel Tank
- Plastic Jacket with 2" Polyurethane Foam Insulation

Optional Equipment

- Double Wall Coil



We provide a full, one-year warranty for the Peerless® Partner® Indirect-Fired Water Heater. We also provide a limited, lifetime warranty against leaks from the heater's jacket, tank, or heat exchanger for residential applications and a limited, five-year warranty against leaks from the heater's jacket, tank or heat exchanger for commercial applications. Please consult us for complete warranty information.



PeerlessBoilers.com



FAB-PARTNER R6 (3/08-6M)
Printed in U.S.A.