

# Braeburn®

## 5320

**Up to 4 Heat / 2 Cool Heat Pump**  
**Up to 3 Heat / 2 Cool Conventional**  
**Programmable or Non-Programmable**  
**Thermostat**



ACTUAL SIZE

**5 YEAR**  
LIMITED  
WARRANTY

## Features

- 7 Day, 5-2 Day or Non-Programmable
- Large 6.5 sq. in. Easy-Read Touchscreen
- Auto or Manual Changeover
- Bright Blue Backlight Display
- SpeedBar® Multi-Function Button
- Residential or Commercial Modes
- Adjustable Temperature Limits
- Indoor or Outdoor Remote Sensing
- SpeedSet™ 7 Day Programming Mode
- User Selectable Service Monitors
- Separate User and Installer Reset Buttons
- Auxiliary Heat Fossil Fuel Option
- Hardwire or Battery Powered
- Multi-Level Keypad Lockout
- Economizer Control
- Circulating Fan Mode
- Programmable Fan Mode
- English / Spanish Packaging and Instruction Card with FREE Contractor Branding


**PREMIER  
SERIES**

FREE Contractor Branding! Visit [braeburnonline.com](http://braeburnonline.com)

Touchscreen  
*hybrid*

Toll-Free 866.268.5599 (U.S.) +1.630.844.1968 (Outside the U.S.)

## Terminal Designations



## Architectural Specifications

The universal auto changeover thermostat shall be a Braeburn® model number 5320, 3.94" high x 5.56" wide x 1.19" deep, powered with either 24 Volt AC or with two "AA" Alkaline batteries (3.0 Volt DC). In the event of a power failure, the unit shall retain clock settings and universal 7 or 5-2 day or non-programmable settings. The thermostat shall be compatible with low voltage single stage or multi-stage gas, oil, or electric conventional heating or cooling systems with up to three stages of heating and two stages of cooling, heat pump systems with up to four stages of heating and two stages of cooling and 250mv – 750mv millivolt heating only systems. The thermostat shall have a bright blue backlight display, touchscreen with SpeedBar®, separate sub-base and multi-level keypad lockout. Temperature control range shall be between 45° and 90° F (7° and 32° C), accuracy of +/- 1° F (+/- .5° C). Operating humidity range between 5% and 95% relative humidity. The thermostat shall include separate installer and user setup modes, residential or commercial setup modes, permanent non-volatile memory to retain user settings, filter, UV and humidifier pad check monitor, adaptive recovery mode (ARM™), programmable independent fan control, residual cooling fan delay, indoor or outdoor remote sensor capability, auxiliary heat fossil fuel programming, and compressor power outage protection. A front reset button will return user settings to default values when pressed. This thermostat shall meet California Title 24 Guidelines.

## Product Specifications

<b>Dimensions:</b>	3.94" x 5.56" x 1.19"
<b>Electric Rating:</b>	24 Volt AC (18-30 Volt AC) 1 amp maximum load per terminal 7 amp total maximum load (all terminals)
<b>AC Power:</b>	18-30 Volt AC
<b>DC Power:</b>	3.0 Volts DC (2 "AA" Alkaline batteries included)
<b>Compatibility:</b>	Heat pump systems up to 4 heat/2 cool, Conventional systems up to 3 heat/2 cool 250mv – 750mv millivolt heating systems
<b>Control Range:</b>	45° to 90° F (7° to 32° C)
<b>Display Range:</b>	40° to 99° F (5° to 37° C)
<b>Accuracy:</b>	+/- 1° F (+/- .5° C)
<b>Temperature Differential:</b>	1st Stage - .5°, 1°, or 2° F (.25°, .5°, or 1° C) 2nd, 3rd and 4th Stage - 1°, 2°, 3°, 4°, 5°, or 6° F (.5°, 1°, 1.5°, 2°, 2.5°, or 3° C)
<b>Storage Temperature:</b>	14° to 140° F (-10° to 60° C)
<b>Operating Humidity:</b>	5% to 95% Relative Humidity
<b>Terminations:</b>	A, G, Rc, Rh, W2/AUX2, W3/O/B, Y1, Y2, W1/E/AUX1, C, L, S1, S2

## Shipping Information

INDIVIDUAL CARTON	MASTER CARTON
<b>Dimensions:</b> 5.0" x 6.3" x 2.0"	<b>Quantity:</b> 6
<b>Weight:</b> 0.9 lbs.	<b>Dimensions:</b> 6.4" x 13" x 5.6"
	<b>Cubic Feet:</b> .27
	<b>Weight:</b> 6 lbs.

## Braeburn 5320 Replaces\*

<b>Honeywell®</b>	TB7220, TB8220, TH8320
<b>White-Rodgers®</b>	1F95-0671, 1F95-0680, 1F95-1277, 1F95-1280, 1F95EZ-0671

\*Verify specific application requirements.  
All trademarks are the property of their respective owners.

## Accessories

2950 Universal Wall Plate (6.5" x 6.5" x .125")	5390 Remote Indoor Sensor
5970 Universal Thermostat Guard	5490 Remote Outdoor Sensor

## FREE Contractor Branding Available!

Visit our website ([www.braeburnonline.com](http://www.braeburnonline.com)) for more information, contact your local distributor or call our sales department toll-free at 866.268.5599 (U.S.), +1.630.844.1968 (Outside the U.S.).

Date: \_\_\_\_\_  
Job Name: \_\_\_\_\_  
Location: \_\_\_\_\_  
Contractor: \_\_\_\_\_

Engineer: \_\_\_\_\_  
Model No.: \_\_\_\_\_  
Submitted By: \_\_\_\_\_  
Submitted For Approval: \_\_\_\_\_ Record: \_\_\_\_\_