

2" Copper Valved Manifold with ProPEX® Ball Valves

Submittal Information

Revision A: Feb. 19, 2008

Project Information

Job Name:

Location:

Engineer:

Contractor:

Manufacturer's Representative:

Part No. Ordered:


Date Submitted:

Submitted By:

Approved By:

Technical Data

Manifold Body:	Type L Copper
Ball Valve:	360 Brass
Manifold Body Size:	2.0"
Maximum Temperature (no pressure):	320°F (160°C)
Maximum Working Temperature/Pressure:	210°F (99°C) at 150 psi
Maximum Flow Rate:	45 gpm
Ball Valve Cv:	5/8" outlet - 7.00 3/4" outlet - 7.30



Product Information and Application Use

The 2" Copper Valved Manifold with ProPEX® Ball Valves is used for radiant heating projects.¹ The manifold has a 2" copper sweat fitting adapter supply connection and 3/4" nominal branches. This 12-outlet manifold is preassembled with 5/8" or 3/4" ProPEX ball valve connections.

✓ Description	Part Number	A	B	C	D	Weight
2" x 4' Copper Valved Manifold with 5/8" ProPEX Ball Valves, 12 outlet	Q2811263	48.0"	6.74"	4.0"	5/8"	15.50 lbs.
2" x 4' Copper Valved Manifold with 3/4" ProPEX Ball Valves, 12 outlet	Q2811275	48.0"	6.80"	4.0"	3/4"	15.50 lbs.

Installation

Any product designed to mount 2" copper pipe may be used as a mounting bracket. Refer to the Uponor Radiant Installation Handbook for additional information. Accessories: 2" Copper Manifold End Cap (A2402000).

Standards

CSA B137.5; ASTM F877

Codes

N/A

Listings

NSF-rfh; NSF 61-certified

Related Applications

Radiant Heating and Cooling Systems

Contact Information

Uponor, Inc.
5925 148th Street West
Apple Valley, MN 55124 USA
Phone: (800) 321-4739
Fax: (952) 891-2008
www.uponor-usa.com

Uponor Ltd.
655 Park Street
Regina, SK S4N 5N1 CANADA
Phone: (888) 994-7726
Fax: (800) 638-9517
www.uponor.ca

¹ProPEX® is a registered trademark of Uponor, Inc. ProPEX™ is a trademark of Uponor Ltd.