



WEL-FLO[®]

Pre-Pressurized Water System Tanks



Multi-Dome Construction

- Deep drawn steel outperforms other designs in pressure tests.

Heavy-Duty Butyl/EPDM Diaphragm

- 30% thicker to outlast the competition.

100% Polypropylene Liner

- Meets NSF[®] International Standard 61 and FDA requirements for clean, safe drinking water.

Hoop Ring & Groove Design

- Provides a permanent seal between diaphragm, liner and domes.

Welded Air Stem

- Ensures reliable, leak-free performance.


5-Year Warranty

Reliable, Durable and Affordable.



WEL-FLO®

Wel-Flo pre-pressurized well tanks deliver reliable performance at an affordable price. All feature a deep-drawn steel dome design, hoop ring and groove construction and a 5-year limited warranty. Made in the USA at our ISO 9001:2008 registered facilities, Wel-Flo well tanks are an outstanding value.



Specifications									
Model Number	Tank Volume (Gallons)	Max. Accept. Volume (Gallons)	A Diameter (Inches)	B Height (Inches)	System Connection NPTF (Inches)	System Drawdown (Gallons)			Shipping Weight (lbs.)
						30/50 PSI	40/60 PSI	50/70 PSI	
WF-14	14	11.3	15	25	1	4.8	4.1	3.3	25
WF-20	20	11.4	15	32	1	6.8	5.9	4.7	33
WF-26	26	11.4	15	39	1	8.8	7.6	6.1	36
WF-32	32	11.2	15	47	1	10.9	9.4	7.6	43
WF-34	34	34.0	22	30	1¼	11.6	10.0	8.0	61
WF-44	44	33.9	22	36	1¼	15.0	12.9	10.4	69
WF-62	62	34.1	22	47	1¼	21.1	18.2	14.6	92
WF-81	81	33.2	22	57	1¼	27.5	23.8	19.1	103
WF-252	86	33.5	22	62	1¼	29.2	25.3	20.3	114
WF-86	86	46.4	26	47	1¼	29.2	25.3	20.3	123
WF-119	119	46.4	26	62	1¼	40.5	35.0	28.1	166

Malleable Iron System Connection.

Maximum Operating Temperatures: 200°F. Factory Pre-Charge: 38 PSI. Maximum Working Pressure: 100 PSI.



Sizing						
Pump Discharge Rate GPM (Approx.)	Pumps Up To 3/4 hp & 1 Minute Run Time			Pumps Over 3/4 hp & 2 Minute Run Time		
	30/50 PSI	40/60 PSI	50/70 PSI	30/50 PSI	40/60 PSI	50/70 PSI
5	WF-20	WF-20	WF-20	WF-34	WF-34	WF-44
7	WF-26	WF-32	WF-32	WF-44	WF-62	WF-62
10	WF-34	WF-34	WF-44	WF-62	WF-81	WF-86
12	WF-44	WF-44	WF-62	WF-81	WF-81	WF-119
15	WF-44	WF-62	WF-62	WF-86	WF-119	WF-119
20	WF-62	WF-81	WF-86	WF-119	WF-81 (2)	WF-86 (2)
25	WF-81	WF-86	WF-119	WF-81 (2)	WF-86 (2)	WF-119 (2)
30	WF-86	WF-119	WF-119	WF-86 (2)	WF-119 (2)	WF-86 (3)
35	WF-119	WF-119	WF-81 (2)	WF-119 (2)	WF-119 (2)	WF-119 (3)
40	WF-119	WF-81 (2)	WF-86 (2)	WF-119 (2)	WF-86 (3)	WF-119 (3)

Larger Tank = Fewer Cycles for Longer Tank and Pump Life



1400 Division Road, West Warwick, RI 02893 USA
T: 800.426.8765 F: 800.293.1519
www.amtrol.com