

Braeburn®

1220NC

Up to 2 Heat / 1 Cool
Conventional and Heat Pump
Non-Programmable Thermostat



Features

- Large 2 Sq. In. Display with Bright Blue Backlight
- Adjustable Temperature Limits
- Hardwire or Battery Powered
- Permanent Memory Retains Settings
- Adjustable Temperature Differential
- Compressor Short Cycle Protection
- Separate O & B Terminals
- Auxiliary Heat Indicator
- Low Battery Indication
- ESD Guard™ Electronic Circuitry
- Front Access Reset Button
- F° / C° Switch
- English / Spanish Packaging and Instruction Card with FREE Contractor Branding


**BUILDER
SERIES**

FREE Contractor Branding! Visit braeburnonline.com

Toll-Free 866.268.5599 (U.S.) +1.630.844.1968 (Outside the U.S.)

Braeburn®

Terminal Designations



Architectural Specifications

The digital non-programmable thermostat shall be a Braeburn® model number 1220NC, 3.62" high x 4.72" wide x 1.38" deep, powered independently with either 24 VAC or two "AA" Alkaline batteries (3.0 Volt DC). The thermostat shall be compatible with multi-stage conventional or heat pump systems with up to two stages of heating and one stage of cooling and heat pump systems with one compressor and up to one auxiliary stage. The thermostat shall have a bright blue backlight display and separate sub-base for trouble free installation. Temperature control range shall be between 45° and 90° F (7° and 32° C), accuracy of +/- 1° F (+/- .5° C), humidity range between 5% and 95% relative humidity. The thermostat shall include non-volatile memory to retain user settings, adjustable temperature limits and auxiliary heat indicator. Thermostat shall have low battery indication and a front reset button will return user settings to default values when pressed. The thermostat can be mounted to a horizontal junction box.

Product Specifications

Dimensions:	3.62" x 4.72" x 1.38"
Electric Rating:	24 Volt AC (18-30 Volt AC) 1 amp maximum load per terminal 3 amp total maximum load (all terminals)
AC Power:	18-30 Volt AC
DC Power:	3.0 Volts DC (2 "AA" Alkaline batteries included)
Compatibility:	Conventional systems up to two stages of heating and one stage of cooling; Heat pump systems with one compressor and up to one auxiliary stage; 250mv - 750mv millivolt heating systems
Control Range:	45° to 90° F (7° to 32° C)
Display Range:	40° to 99° F (5° to 37° C)
Accuracy:	+/- 1° F (+/- .5° C)
Temperature Differential:	1st Stage - .5°, 1°, or 2° F (.25°, .5°, or 1° C) 2nd Stage - 2°, 3°, 4°, 5°, or 6° F (1°, 1.5°, 2°, 2.5°, or 3° C)
Storage Temperature:	14° to 140° F (-10° to 60° C)
Operating Humidity:	5% to 95% Relative Humidity
Terminations:	Rh, Rc, O, B, Y, E/W1, G, C, W2

Shipping Information

INDIVIDUAL CARTON	MASTER CARTON
Dimensions: 3.8" x 5.8" x 1.6"	Quantity: 12
Weight: .70 lbs.	Dimensions: 11" x 11.7" x 4.3"
	Cubic Feet: .32
	Weight: 9.2 lbs.

Braeburn 1220NC Replaces*

Honeywell®	TH2210
White-Rodgers®	1F79-111

*Verify specific application requirements.
All trademarks are the property of their respective owners.

Accessories

2950 Universal Wall Plate (6.5" x 6.5" x .125")
5970 Universal Thermostat Guard

FREE Contractor Branding Available!

Visit our website (www.braeburnonline.com) for more information, contact your local distributor or call our sales department toll-free at 866.268.5599 (U.S.), +1.630.844.1968 (Outside the U.S.).

Date: _____
 Job Name: _____
 Location: _____
 Contractor: _____

Engineer: _____
 Model No.: _____
 Submitted By: _____
 Submitted For Approval: _____ Record: _____

Braeburn Systems LLC • 2215 Cornell Avenue • Montgomery, IL 60538 • Toll-Free 866.268.5599 (U.S.) +1.630.844.1968 (Outside the U.S.)