INSTALLATION MANUAL



TRUE COMFORT ||||

This manual covers the following models:

• T905



Thermostat Applications Guide

Description	
Gas or Oil Heat	Yes
Electric Furnace	Yes
Heat Pump (No Aux. or Emergency Heat)	Yes
Heat Pump (with Aux. or Emergency Heat)	No
Multi-stage Systems	No
Heat Only Systems	Yes
Cool Only Systems	Yes
Millivolt	Yes

Power Type

Battery Power
Hardwire (Common Wire)
Hardwire (Common Wire) with Battery Backup

Table of Contents Page Installation Tips 2 Thermostat Quick Reference 3 Subbase Installation 4 5 Wiring 6 Wiring Diagrams Technician Setup Menu 7-9 10 Mounting and Battery Installation 11-13 Programming The Thermostat Specifications 14

Una versión española de este manual puede ser descargada en www.pro1iaq.com

A trained, experienced technician must install this product.


Carefully read these instructions. You could damage this product or cause a hazardous condition if you fail to follow these instructions.

Need Help?

For assistance with this product please visit http://www.pro1iaq.com or call Pro1 Customer Care toll-free at 888-Pro1iaq (776-1427) during normal business hours (Mon-Fri 9 AM - 6 PM Eastern)

Wall locations

The thermostat should be installed approximately 4 to 5 feet above the floor. Select an area with average temperature and good air circulation.



Do not install thermostat in locations:

- Close to hot or cold air ducts
- That are in direct sunlight
- With an outside wall behind the thermostat
- In areas that do not require conditioning
- Where there are dead spots or drafts (in corners or behind doors)
- Where there might be concealed chimneys or pipes

PRO1 Tip

Pick an installation location that is easy for the user to access. The temperature of the location should be representative of the building.

THERMOSTAT QUICK REFERENCE

Getting to know your thermostat





Important:

The low battery indicator is displayed when the AA battery power is low. If the user fails to replace the battery within 21 days, the thermostat display will only show the low battery indicator as a final warning before the thermostat becomes inoperable. The batteries are located on the back of the thermostat.

1 LCD

Days of the

week and time

- ② Glow in the Dark Light Button
- 3 Fan Button
- 4 System Button
- 5 Temperature Setpoint Buttons
- 6 Menu Button

Low Battery Indicator: Replace batteries when this indicator is shown.

Programmable Time Period Icons:

This thermostat has 4 programmable time periods per day.

Clean Display:

Pressing CLEAN DISPLAY will allow 30 seconds to clean the display. The keys will be inoperable during this time. CLEAN will appear if your contractor has programmed a filter change reminder. Press CLEAN when filter has been replaced to reset the filter change reminder timer.

Indicates the current room temperature.

Displays the user selectable setpoint temperature.

HOLD is displayed when thermostat program is permanently overridden.

System operation indicators: The COOL, HEAT or FAN icon will display when the COOL, HEAT or FAN is on.


NOTE: The compressor delay feature is active if these icons are flashing. The compressor will not turn on until the 5 minute delay has elapsed.



Program Menu Options: Shows different options

during programming.

Removing the private label badge



Gently slide a screwdriver into the bottom edge of the badge. Gently turn the screwdriver counter clockwise. The badge is held on by a magnet. The badge should pry off easily. **Do not use force.**

All Pro1 thermostats use the same universal magnetic badge.

Visit our website at www.pro1iaq.com to learn more about our free private label program.

SUBBASE INSTALLATION



Caution: Electrical Hazard

Failure to disconnect the power before beginning to install this product can cause electrical shock or equipment damage.



Mercury Notice:

All of Pro1's products are mercury free. However, if the product you are replacing contains mercury, dispose of it properly. Your local waste management authority can give you instructions on recycling and proper disposal.

For vertical mount put one screw top and one screw bottom. Vertical mount For horizontal mount put one screw left and one screw right. 同 同 **UP** Horizontal mount Horizontal mount 個 ГД Vertical mount



Caution: Electrical Hazard

Failure to disconnect the power before beginning to install this product can cause electrical shock or equipment damage.



Warning:

All components of the control system and the thermostat installation must conform to Class II circuits per the NEC Code.

Wiring

- 1. If you are replacing a thermostat, make note of the terminal connections on the thermostat that is being replaced. In some cases the wiring connections will not be color coded. For example, the green wire may not be connected to the **G** terminal.
- 2. Loosen the terminal block screws. Insert wires then retighten terminal block screws.
- 3. Place nonflammable insulation into wall opening to prevent drafts.

Terminal Designations

- W Heat relay
- Y Compressor relay
- G Fan relay
- Heat pump changeover valve energized in cooling
- **RC** Transformer power for cooling

RH Transformer power for heating

- Heat pump changeover valve energized in heating
- C Common wire from secondary side of cooling system transformer or for heat only system transformer

PRO1 Tips:

RH & RC terminals

For single transformer systems, leave the jumper wire in place between RH and RC. Remove jumper wire for two transformer systems.

Heat pump systems

If wiring to a heat pump, use a small piece of wire (not supplied) to connect terminals W and Y.

C terminal

The C (common wire) terminal does not have to be connected when the thermostat is powered by batteries.


Wire specifications

Use shielded or non-shielded 18 - 22 gauge thermostat wire.

WIRING DIAGRAMS


- Power supply
- A Factory-installed jumper. Remove only when installing on 2-transformer systems.
- Use either O or B terminals for changeover valve.
- Use a small piece of wire (not supplied) to connect W and Y terminals.
- **Set** fan operation switch to electric
- Optional 24 VAC common connection when thermostat is used in battery power mode.


Typical 1H/1C system: 1 transformer




Typical 1H/1C heat pump system

Typical heat-only system with fan







Typical 1H/1C system: 2 transformer



Typical heat-only system



Typical cool-only system



TECHNICIAN SETUP MENU

Technician Setup Menu

This thermostat has a technician setup menu for easy installer configuration. To set up the thermostat for your particular application:

- 1. Press **MENU** button
- 2. Press and hold **TECHNICIAN SETUP** button for 3 seconds. This 3 second delay is designed so that homeowners do not accidentally access the installer settings.
- 3. Configure the installer options as desired using the table below.

Use the

to respect to the least to the lea

Tech Setup S	teps					
Filter Change Reminder	Room Temperature Calibration	Minimum Compressor On Time	Compressor Short Cycle Delay	Cooling Swing	Heating Swing	Keypad Lockout
This feature will flash FILT in the display after the elapsed run time to remind the user to change the filter. A setting of OFF will disable this feature.	This feature allows the installer to change the calibration of the room temperature display. For example, if the thermostat reads 70° and you would like it to read 72° then select +2.	This feature allows the installer to select the minimum run time for the compressor. For example, a setting of 4 will force the compressor to run for at least 4 minutes every time the compressor turns on, regardless of the room temperature.	The compressor short cycle delay protects the compressor from "short cycling". This feature will not allow the compressor to be turned on for 5 minutes after it was last turned off.	The swing setting, often called "cycle rate", "differential" or "anticipation" is adjustable. A smaller swing setting will cause more frequent cycles and a larger swing setting will cause fewer cycles.	The swing setting, often called "cycle rate", "differential" or "anticipation" is adjustable. A smaller swing setting will cause more frequent cycles and a larger swing setting will cause fewer cycles.	Keypad lockout allows you to configure the thermostat so that none or some of the keys do not function.
LCD Will Show	SO SOLDANIS				## dF \ HE	
Adjustment Options						
You can adjust the filter change reminder from OFF to 2000 hours of runtime in 50 hour increments.	You can adjust the room temperature display to ready -4°F to +4°F above or below the factory calibrated reading.	You can select the minimum compressor run time from "off", "3", "4", or "5" minutes. If 3, 4, or 5 is selected, the compressor will run for at least the selected time before turning off.	Selecting ON will not allow the compressor to be turned on for 5 minutes after the last time the compressor was on. Select OFF to remove this delay.	The cooling swing setting is adjustable from ±0.4°F to ±2°F. For example: A swing setting of 0.5°F will turn the cooling on at approximately 0.5°F above the setpoint and turn the cooling off at approximately 0.5°F below the setpoint.	The heating swing setting is adjustable from ±0.4°F to ±2°F. For example: A swing setting of 0.5°F will turn the heating on approximately 0.5°F below the setpoint and turn the heating off at approximately 0.5°F above the setpoint.	Pick PA or FU PA = partial keypad lockout, which locks all the keys except th → or keys. FU = Full keypad lockout, which locks out all the keys. Note: Keypad lockout instructions are below
Factory Default Setting		055	O.V.	0.5.05	0.4.05	NA
0FF	0 °F	OFF	ON	0.5 °F	0.4 °F	NA

Note: To lock the keypad hold down the \triangle and ∇ keys for 3 seconds. You will see a lock in the display. To unlock the keypad hold down the \triangle and ∇ keys for 3 seconds.



TECHNICIAN SETUP MENU

Heating Temperature Setpoint Limit	Cooling Temperature Setpoint Limit	°F or °C	12 or 24 Hour Clock	Fan Operation	Morning Recovery	Program Options
This feature allows you to set a maximum heat setpoint value. The setpoint temperature cannot be raised above this value.	This feature allows you to set a minimum cool setpoint value. The setpoint temperature cannot be lowered below this value.	Select F for Fahrenheit temperature read out or select C for Celsius read out	You can select either a 12 or 24 hour clock setting.	Select GAS for systems that control the fan during a call for heat. Select ELEC to have the thermostat control the fan during a call for heat.	This feature turns your system on before the WAKE programming time to ensure the enviroment is at the WAKE setpoint when the WAKE time period begins. This recovery changes over time based on the previous day's experience.	You can configure this thermostat to have a 7 day program, a 5+1+1 program or nonprogrammable.
LCD Will Show						
			ISH ⇔	6.R5		5d
Adjustment Options						
Jse the or contact of the contact of	Use the ← or key to select the minmum cool setpoint.	°F for Fahrenheit °C for Celsius	Use the 🚭 or 🗁 key to select 12 or 24 hour clock.	GAS or ELEC	Use the 🚭 or 🗁 key to turn on or off.	Use the or be key to select 7d for 7d day, 5d for 5+1+1 or 0d for nonprogammable.
actory Default Settings						
90 °F	44 °F	°F	12 Hour Clock	GAS	ON	5d



PRO1 Tip

Temperature swing, sometimes called differetial or cycle rate, can be customized for this individual application. For most applications choose a swing setting that is as long as possible without making the occupants uncomfortable.

TECHNICIAN SETUP MENU

Tech Setup Ste	Tech Setup Steps (Continued from the previous page)				
Display Light	Contractor Call Number	Веер	System Switch		
The display light can be configured to come on when any key is pressed or only when the light key is pressed.	Allows you to put your phone number in the display. Select ON to use this feature then press NEXT STEP.	When any key is pressed an audible beep will sound. There is an ON or an OFF.	You can configure the system switch for the particular application: Heat - Off - Cool, Heat - Off, Cool - Off, Heat - Off - Cool-Auto		
LCD Will Show					
Adjustment Options					
OFF configures display light to come on only with the light key, which will save battery power. ON configures the display light to come on when any key is pressed.	Use the or low key to move from one character to another. Use the or very key to change the flashing character to your desired number.	If ON is selected the beep will sound. If OFF is selected, there is no sound.	Use the or key until the desired application is flashing.		
Factory Default Settings					
ON	OFF	ON	Heat - Off - Cool		

Note: If Contractor Call Number is selected **ON**, your phone number will show in the display if there has been a continuous call for heating or cooling for 24 hours or if the light button is held down for 3 seconds. To remove the phone number from the display, hold the light button down for 3 seconds.

MOUNT THERMOSTAT & BATTERY INSTALLATION


Mount Thermostat


Align the 4 tabs on the subbase with corresponding slots on the back of the thermostat, then push gently until the thermostat snaps in place.



Battery Installation

Battery installation is optional if thermostat is hardwired (C terminal connected).





2 AA Alkaline batteries (included).

PROGRAMMING THE THERMOSTAT

Set Time

Follow the steps below to set the day of the week and current time:

- 1. Press MENU
- 2. Press SET TIME
- 3. Day of the week will be flashing. Use the + or key below the time setting to select the current day of the week.
- 4. Press **NEXT STEP**
- 5. The current hour is flashing. Use the to select the current hour. When using 12-hour time, make sure the correct a.m. or p.m. choice is selected.
- 6. Press NEXT STEP
- 7. Minutes are now flashing. Use the + or key below the time setting to select current minutes.
- 8. Press DONE when completed

Programming

All programmable Pro1 thermostats are shipped with an energy saving pre-program. You can customize this default program by following the Set Program Schedule.

Your thermostat can be programmed to have each day of the week programmed uniquely (7 days), all the weekdays the same, a separate program for Saturday, and a separate program for Sunday (5+1+1), or nonprogrammable. There are four time periods for each program (**WAKE, LEAVE, RETURN, SLEEP**). This thermostat has a programmable fan feature, which allows you to run the fan continuously during any time period.

Factory Default Program				
Day of the Week	Events	Time	Setpoint Temperature (Heat)	Setpoint Temperature (Cool)
Weekday	Wake 🕍	6 a.m.	70° F (21° C)	75° F (24° C)
	Leave 👬	8 a.m.	62° F (17° C)	83° F (28° C)
	Return in fi	6 p.m.	70° F (21° C)	75° F (24° C)
	Sleep 🐪	10 p.m.	62° F (17° C)	78° F (26° C)
Saturday	Wake 🚮	8 a.m.	70° F (21° C)	75° F (24° C)
	Leave 👬	10 a.m.	62° F (17° C)	83° F (28° C)
	Return +	6 p.m.	70° F (21° C)	75° F (24° C)
	Sleep 🐪	11 p.m.	62° F (17° C)	78° F (26° C)
Sunday	Wake 🕌	8 a.m.	70° F (21° C)	75° F (24° C)
	Leave 👬	10 a.m.	62° F (17° C)	83° F (28° C)
	Return 👬	6 p.m.	70° F (21° C)	75° F (24° C)
	Sleep 👚	11 p.m.	62° F (17° C)	78° F (26° C)

PROGRAMMING THE THERMOSTAT

You can use the table below to plan your customized program schedule if using 5+1+1.

	Programming Table				
Day of the Week	Events	Time	Setpoint Temperature (Heat)	Setpoint Temperature (Cool)	
Weekday	Wake 🕌				
	Leave diff				
	Return in the				
	Sleep 👚				
Saturday	Wake 🕍				
	Leave (iff				
	Return in				
	Sleep 👚				
Sunday	Wake 🔏 🕆				
	Leave 41				
	Return in				
	Sleep 👚				

Set Program Schedule

To customize your 5+1+1 program schedule, follow these steps:

Weekday:

- Select HEAT or COOL using the SYSTEM key.
 Note: You have to program heat and cool each separately.
- 2. Press MENU
- 3. Press **SET SCHEDULE** Note: Monday-Friday is displayed and the **WAKE** icon is shown. You are now programming the **WAKE** time period for the weekday setting.
- 4. Use the
 or
 key below the time setting to make your time selection for the weekday **WAKE** time period. Note: If you want the fan to run continuously during this time period, select **ON** with the **FAN** key.
- 5. Use the $\stackrel{\frown}{\checkmark}$ or $\stackrel{\frown}{\lor}$ temperature setpoint keys on the right side of your screen to make your temperature selection for the weekday **WAKE** period.
- 6. Press **NEXT STEP**
- 7. Repeat steps 4 through 6 for weekday **LEAVE** time period, for weekday **RETURN** time period, and for weekday **SLEEP** time period.

Saturday:

 Repeat steps 4 through 6 for Saturday WAKE time period, for Saturday LEAVE time period, for Saturday RETURN time period, and for Saturday SLEEP time period.

Sunday:

9. Repeat steps 4 through 6 for Sunday **WAKE** time period, for Sunday **LEAVE** time period, for Sunday **RETURN** time period, and for Sunday **SLEEP** time period.

PROGRAMMING THE THERMOSTAT

To customize your 7 day program schedule, follow these steps:

- 1. Select **HEAT** or **COOL** using the **SYSTEM** key. You have to program heat and cool each separately.
- 2. Press MENU
- Press SET SCHEDULE
 Note: Monday is displayed and the WAKE icon is shown. You are now programming the WAKE time period for the Monday setting.
- 4. Use the

 + or

 key below the time setting to make your time selection for the weekday

 WAKE time period. Note: If you want the fan to run continuously during this time period, select ON
 with the FAN key.
- 6. Press **NEXT STEP**
- Repeat steps 4 thru 6 for Monday LEAVE time period, for Monday RETURN time period, and for Monday SLEEP time period.
- 8. Repeat steps 4 thru 7 for each of the remaining days in the week.

A Note About Auto Changeover:

Auto changeover will switch between heating and cooling as needed. It is very important to make sure the cooling setpoint temperature is at least 3° above the heating setpoint temperature and that the heating setpoint temperature is at least 3° below the cooling setpoint temperature.

A Note About Programmable Fan:

The programmable fan feature will run the fan continuously during any time period it is programmed to be on. This is the best way to keep the air circulated and to eliminate hot & cold spots in your building.

SPECIFICATIONS & CONTACT INFORMATION

Specifications

The display range of temperature The control range of temperature Load rating	
Display accuracy	• •
Swing (cycle rate or differential)	- · · · · · · · · · · · · · · · · · · ·
	Cooling is adjustable from 0.4°F to 2.0°F
Power source	. 18 to 30 VAC, NEC Class II, 50/60 Hz for hardwire (common wire) Battery power from 2 AA Alkaline Energizer batteries
Operating ambient	. 32° to +105° (0° to +41°C)
Operating humidity	S Comment of the comm
Dimensions of thermostat	. 4.7"W x 4.4"H x 1.1"D

Contact Us

Pro1 IAQ Inc.

1111 S. Glenstone Suite 2-100 Springfield, MO 65804

Toll-free: 1-888-Pro1iaq (776-1427)

Toll Number (Outside the USA): 330-821-3600

Web: http://www.pro1iaq.com

Hours of Operation: Monday - Friday 9 AM - 6 PM Eastern