

Submittal Data Information

101-031

Model 008 Cartridge Circulator

Supersedes: September 1, 2003 Effective: May 8, 2009

Job: Eng	C	ontractor:		Rep:			
ITEM NO.	MODEL NO.	IMP. DIA.	G.P.M.	HEAD/FT.	H.P.	ELEC. CHAR.	

Features

- Standard High Capacity Output-Compact Design
- Quiet, Efficient Operation
- Direct Drive-Low Power Consumption
- Unique Replaceable Cartridge Design-Field Serviceable
- Self Lubricating
- No Mechanical Seal
- · Unmatched Reliability-Maintenance Free
- Universal Flange to Flange Dimensions
- Cast Iron or Stainless Steel, Flanged or Bronze, Sweat Connections

Materials of Construction

Casing (Volute): Cast Iron or St. Steel, Flanged

Bronze, Sweat

Stator Housing: Steel

Cartridge: Stainless Steel Impeller: Non-Metallic Shaft: Ceramic Carbon Bearings: O-Ring & Gaskets: EPDM

Model Nomenclature

F - Cast Iron, Flanged

SF - Stainless Steel, Flanged

BC - Bronze, 3/4"Sweat Connections

Variations:

Z - Zoning Circulator

J - Bronze Cartridge with Cast Iron Casing

Performance Data

Flow Range: 0 - 14 GPM Head Range: 0 - 16 Feet

Minimum Fluid Temperature: 40°F (4°C) Maximum Fluid Temperature: 230°F (110°C)

Maximum Working Pressure: 125 psi

Connection Sizes: 3/4", 1", 1-1/4", 1-1/2" Flanged, 3/4" Sweat

LISTED


FOR INDOOR USE ONLY


Application


The Taco 008 is designed for a wide range of residential and light commercial higher-head water circulating applications. Typical uses include hydronic heating, radiant in-floor/panel heating and closed-loop solar heating systems. The Stainless Steel or Bronze 008 can be used in higher-head heat recovery, water source heat pump, open-loop solar heat and domestic water recirculation systems. The unique replaceable cartridge contains all of the moving parts and allows for easy service, instead of replacing the entire circulator. Compact, direct-drive, low power consumption design is ideal or high-efficiency jobs.

Pump Dimensions & Weights

		A	١	ВС		D	D		F		G		Ship Wt.		
Model	Casing	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	lbs.	Kg
008-F6	Cast Iron	6	152	4	102	3-3/16	81	2-15/16	75	4-3/4	121	6-3/8	162	8.0	3.6
008-SF6	St. Steel	6	152	4	102	3-3/16	81	2-15/16	75	4-3/4	121	6-3/8	162	8.0	3.6
008-BC6	Bronze	5-5/8	143	4-9/16	116	3-3/16	81	2-15/16	75	4-3/4	121	6-3/8	162	8.0	3.6










Electrical Data


Model	Volts	Hz	Ph	Amps	RPM	HP				
008-F6	115	60	I	.79	3250	1/25				
008-SF6	115	60	- 1	.84	3250	1/25				
008-BC6	115	60	I	.84	3250	1/25				
Motor Type		Permanent Split Capacitor Impedance Protected								
Motor Options 220/50/1, 220/60/1, 230/60/1, 100/110/50/0										

Flange Orientation



Fax: (905) 564-9436

Performance Field - 60Hz



Do it Once. Do it Right.®

Visit our website at: www.taco-hvac.com

TACO INC., 1160 Cranston Street, Cranston, RI 02920 Telephone: (401) 942-8000 Fax: 942-2360 TACO (Canada), Ltd., 6180 Ordan Drive, Mississauga, Ontario L5T 2B3 Telephone: (905) 564-9422

Printed in USA Copyright 2009 TACO, Inc.