

THIS SPACE FOR DESIGNER/ENGINEER APPROVAL

| | | |
|-------------------------|------------|------------------------|
| Job/Customer _____ | Date _____ | Contractor _____ |
| Model Specified _____ | Qty _____ | Approved By _____ |
| Designer/Engineer _____ | Date _____ | Contractor's PO# _____ |
| Submitted by _____ | Date _____ | Other _____ |

5404 Series

Isolator® E-X-P E2™ w/ CleanBrass Construction
Tankless Water Heater Service Valve Kits
Hot & Cold Set of Full Port Forged Brass Ball Valves
w/ Hi-Flow Hose Drains & Pressure Relief Valve Outlet
IPS Union x SWT
500 WOG

Includes Residential or Commercial Pressure Relief Valve

The ISOLATOR®
E·X·P E2
TWH SERVICE VALVES

LEAD FREE
CLEAN BRASS
THE CLEAR CHOICE FOR THE PROFESSIONAL


| ITEM # | SIZE | CTN | CASE | A | B | C | D | E | F | G |
|---|------|-----|------|-----|-------|-------|-------|-------|-----|-----|
| RESIDENTIAL PRESSURE RELIEF VALVE (150 PSI/200,000 BTU) | | | | | | | | | | |
| 54043PR | 3/4 | 1 | 10 | 3/4 | 4 3/4 | 1 5/8 | 2 5/8 | 2 3/4 | 3/4 | 1/2 |
| 54044PR | 1 | 1 | 10 | 1 | 5 1/8 | 2 3/8 | 2 3/8 | 2 3/4 | 3/4 | 3/4 |
| COMMERCIAL PRESSURE RELIEF VALVE (150 PSI/2,703,000 BTU) & 3/4" CLOSE NIPPLE | | | | | | | | | | |
| 54043PR2 | 3/4 | 1 | 6 | 3/4 | 4 3/4 | 1 5/8 | 2 5/8 | 2 3/4 | 3/4 | 1/2 |
| 54044PR2 | 1 | 1 | 6 | 1 | 5 1/8 | 2 3/8 | 2 3/8 | 2 3/4 | 3/4 | 3/4 |



PATENTED TECHNOLOGY
The service valves in these kits are certified to **NSF/ANSI 61-G**

| NO. | DESCRIPTION | MATERIAL |
|-----|--------------------------|-----------------------------------|
| 1 | BODY | BRASS |
| 2 | SEATS | PTFE |
| 3 | BALL | BRASS HCP |
| 4 | HANDLE NUT | STAINLESS STEEL |
| 5 | WING STYLE "T" HANDLE | STEEL CP |
| 6 | HANDLE JACKET | VINYL |
| 7 | PACKING GLAND | BRASS |
| 8 | STEM SEAL | PTFE |
| 9 | STEM | BRASS |
| 10 | END CAP | BRASS |
| 11 | UNION NUT | BRASS |
| 12 | RETAINING RING | STAINLESS STEEL |
| 13 | UNION FITTING | BRASS |
| 14 | WASHER | EPDM |
| 15 | DRAIN VALVE HANDLE | ENAMEL COATED ALUMINUM |
| 16 | DRAIN VALVE HANDLE SCREW | BRASS |
| 17 | CAP & STRAP | BRASS W/ EPDM HOSE WASHER & STRAP |

| TEMP °F | PSI |
|---------|-----|
| 100 | 500 |
| 150 | 408 |
| 180 | 398 |



| Included w/ 5404PR | Included w/ 5404PR2 |
|--|---|
| <p>Residential Pressure Relief Valve (150 PSI / 200,000 btu)</p> | <p>Commercial Pressure Relief Valve (150 PSI / 2,703,000 btu) & 3/4" Close Nipple</p> |

Specifications: Designed for residential or commercial use with potable water. This approved Webstone valve is actuated by a blowout proof stem and features an adjustable packing gland. Solder joint temperature ratings are per ASME B16.18 Annex A for 95-5 solder. Other solder materials have lower pressure/temperature limits. Do not silver braze or overheat valves when soldering.

Webstone
VALVE INNOVATION

Quality and Commitment Since 1954

www.webstonevalves.com · P: (800) 225-9529 · F: (800) 336-5133

Webstone product specifications in U.S. customary units are approximate and are provided for reference only. Webstone reserves the right to change or modify product design, construction, specifications or materials without prior notice and without incurring any obligation to make such changes and modifications on Webstone products previously or subsequently sold.

5404spec_062112