



EPOXY RETENTION


FEATURES:

- Heavy gauge steel construction
- Baked epoxy coating on both interior and exterior
- Epoxy coating complies with F.D.A.
- Tested to 100 psig (air)
- Maximum working pressure - 75 psig
- 3 Year limited warranty
- Same fittings as galvanized tank allowing for easy replacement
- Perfect for pump tank applications




Epoxy Retention Tanks - Desert Tan Color

Model No.	Volume (Gallons)	Tank Dimensions (in inches)										Maximum Acceptance	System Drawdown Volume (Gallons)			
		A	B	C	D	E	F	G	H	J	20/40		30/50	40/60	50/70	
ERTG12-A	12	12	24	26.5	5	13	—	—	1¼	1¼	100%	1.9	1.2	0.9	0.6	
ERTG21-A	21	16	24	26.9	5	13	—	—	1¼	1¼	100%	3.3	2.1	1.5	1.1	
ERTG30-A	30	16	36	38.8	8	17	—	—	1¼	1¼	100%	4.7	3.0	2.2	1.6	
ERTG42T-A	42	16	48	51	12	26	—	—	1¼	1¼	100%	6.5	4.2	3.0	2.2	
ERTG42S-A	42	20	30	33.6	8	17	—	—	1¼	1¼	100%	6.5	4.2	3.0	2.2	
ERTG82-A	82	20	60	63	12	33	—	—	1¼	1¼	100%	12.7	8.2	5.9	4.3	
ERTG120-A	120	24	60	64.5	12	33	—	—	1½	1½	100%	18.6	12.1	8.6	6.3	
ERTG220-A	220	30	66	78	6	32	6	24.3	2	2	100%	34.1	22.2	15.8	11.7	
ERTG315-A	315	36	66	79.5	6	32	7	30.5	2	2	100%	48.8	32.0	22.7	16.7	



ERTG12-A through ERTG120-A



ERTG220-A and ERTG315-A

AMTROL Headquarters
1400 Division Road
West Warwick, RI USA 02893
Telephone: 401.884.6300



AMTROL Canada, Ltd.
275 Shoemaker Street
Kitchener, Ontario N2E 3B3
Telephone: 519.748.1138